

# 18V POLE HEDGETRIMMER 50CM LXT

## DUN500WZ

DUN500W is a 500mm cordless pole hedge trimmers powered by 18V LXT Li-Ion battery



### TECHNICAL SPECIFICATIONS

Battery Type	Li-ion
Body only machine	✓
Voltage	18 v
Blade Length	500 mm
Blade type	Double Sided
Max Branch Diameter	23.5 mm
Strokes per Minute	2,000 / 3,600 / 4,400 spm
Overall Length	2,115 mm
Net weight	3.9 - 4.3 kg
Noise sound pressure	81.5 dB(A)
Noise sound power	92.5 dB(A)
Noise K factor	3 dB(A)
Vibration: Left Handle (Front grip)	4.7 m/sec <sup>2</sup>
Vibration: Right Handle (Rear grip)	2.5 m/sec <sup>2</sup>
Vibration K factor	1.5 m/sec <sup>2</sup>

### USER BENEFITS

- Brushless motor
- Electric brake
- 3-Speed settings (Hi/Med/Low)
- Constant speed control
- Reverse switch
- 180° foldable for easy transport and storage
- New triple-edged cutting teeth are designed to easily catch and firmly hold branches. Curved blades reduce friction resistance to suppress energy loss. Due to the low resistance run time is increased.
- Lightweight
- Two-handed grip
- Angle adjustable hedge trimmer head: 6 angle settings through 115°
- 45° tilt-up to 70° tilt-down from the horizontal position
- Automatic off function: The tool automatically turns off if not operated for a certain period

[Link to product - makitauk.com](https://www.makita.com)



# RELATED PRODUCTS

(Recom

## ■ OTHER