

FEATURES

- **Sintered Bronze Material:** Provides high wear resistance and longevity
- **Flanged Design:** Ensures easy installation and secure fitment
- **Dynamic Load Rating of 14 N/mm²:** Suitable for dynamic applications with moderate loads
- **Static Load Rating of 50 N/mm²:** Capable of handling high static loads
- **16.02 mm Bore Size:** Fits standard shafts for versatile use
- **20.05 mm Outside Diameter:** Compact size for space-constrained environments

RS PRO 16.02 mm Flanged Plain Bearing

RS Stock No: 529-038



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flanged plain bearing is designed for applications requiring reliable and efficient rotational movement. Made from sintered bronze, it offers excellent durability and performance in various industrial settings. Its primary benefit is the ability to support both radial and axial loads, making it ideal for machinery and equipment where space is limited.

General Specifications

Bore Size	16.02 mm
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	20.05 mm
Width	16 mm

Approvals

Standards/Approvals	ISO 2795, ISO 9001:2008, UKAS 001
---------------------	-----------------------------------