



Fuse-link, LV, 100 A, AC 500 V, BS88/B1, 21 x 126 mm, gL/gG, BS

Catalog No. **CD100**

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			low voltage
Rated current	I	A	100
Rated voltage			AC 500 V
Construction size			BS88/B1
Size			21 x 126 mm
Utilization category			gL/gG
Breaking Capacity		kA	80
usable for size/applications			general industrial applications
Standard/Approval			BS
Shape			centre-bolted tags
Standards/Regulations			BS88-2 IEC 60269-2
Optional accessories			fuse-holder RS200

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015])			
Construction size			Other
Rated current		A	100
Rated voltage		V	500
Voltage type			AC
Rated switching capacity		kA	80
Utilization category			gL/gG (cable protection/equipment protection)
Type of fuse status indicator			None
Insulated metal gripping lugs (IMGL)			No

Additional product information (links)

Product datasheet (pdf)	http://www1.cooperbusmann.com/pdf/f8417af7-9f84-4ac5-a79d-b86f6e5b3603.pdf
-------------------------	---