

Starter Kit

13,700 €*



*special offer price plus VAT, installation and training; valid until 31.03.2022

Ersa HR 500

Professional Rework now at 13,700 €

The Ersa HR 500 Hybrid Rework System is the first choice for all common rework tasks on medium-sized SMD assemblies. The system is suitable for desoldering, placing and soldering PLCC, QFP and BGA components as well as MLF components or bipolar elements up to an edge length of 1 x 1 mm. Like all Ersa Hybrid Rework systems, the HR 500 is equipped with a powerful hybrid top heater and highly dynamic infrared heating elements in the bottom emitter (in two switchable zones).

Technical highlights:

- 900 W Hybrid high power heating element
- Full-area 1,600 W IR bottom heater
- High-definition cameras for placement and reflow process observation

Order no.	Description
-----------	-------------

0ACTION-HR500	Ersa HR 500 Promotion Package, complete with Ersa i-CON NANO, 230 V (0IC1200A), Soldering tip 102 Z, 10 mm (0102ZDLF100), Soldering tip 102 W, 2.3 mm (0102WDLF23), Soldering tip 102 W, 3.5 mm (0102WDLF35), Tip fastener, complete for tip series 102 (3IT1040-00), Reflector tape, 25 mm x 1000 mm (0IR4500-40) Flux-Pen IF 6000, for lead free Rework (4FMJF6000-PB), Flux gel, for Rework (5 ml) (4FMJF8300-00), Flux remover, with brush (400 ml) (0FR400)
---------------	---

*special offer price plus VAT, installation and training; valid until 31.03.2022

i-CON NANO 	Soldering tip 102 Z, 10 mm 	Soldering tip 102 W, 2.3 mm 	Soldering tip 102 W, 3.5 mm 	Tip fastener 	Flux-Pen IF 6000 	Flux gel
					Reflector tape 	Flux remover

