

53729

Pipe Exterior Brush, 360 mm, Medium, Black



The brush is suitable for cleaning pipes up to 100 mm in outer diameter. The brush head can be adjusted to fit the individual pipe diameter.

Technical Data

Item Number	53729
Material	Polyester Stainless Steel Polypropylene
Suitable for Food Contact (EU 1935/2004), DoC ¹	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of Phthalates (e.g. Bisphenol A)	No
Is Halal compliant	Yes
Box Quantity	10 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	320 Pcs
Quantity Per Layer (Pallet)	60 Pcs.
Box Length	545 mm
Box Width	270 mm
Box Height	220 mm
Product Diameter	55 mm
Length	360 mm
Width	200 mm
Height	55 mm
Gross Weight	0,2 kg
Net Weight	0,16 kg
Cubik metre	0,003 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max usage temperature (food contact)	80 °C
Max usage temperature (non food contact)	80 °C
Min. usage temperature	-20 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
Gtin-13 Number	5705022002630
GTIN-14 Number (Box quantity)	15705028002662
Commodity Code	96039099
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

1. See Declaration of Compliance for further details on food contact