

7MH5114-5DL60



Siwarex WL270 Load Cell K-S CA SAFE 13 t - Rated Load 13 t - with double bridge - Accuracy 0,1 % - 15m Cable length, 4 Wires - Made of Steel, coated - protection class IP66

List Price	Show prices
Customer Price	Show prices
Service & Support (Manuals, Certificates, FAQs...)	Download

Image similar

Product

Article Number (Market Facing Number)	7MH5114-5DL60
Product Description	Siwarex WL270 Load Cell K-S CA SAFE 13 t - Rated Load 13 t - with double bridge - Accuracy 0,1 % - 15m Cable length, 4 Wires - Made of Steel, coated - protection class IP66
Product family	Load cell
Product Lifecycle (PLM)	PM300:Active Product

Price data

Price Group	8W5
List Price	Show prices
Customer Price	Show prices
Surcharge for Raw Materials	None
Metal Factor	None

Delivery information

Export Control Regulations	AL : N / ECCN : N
Standard lead time ex-works	125 Day/Days
Net Weight (kg)	0,400 Kg
Package size unit of measure	Not available
Quantity Unit	1 Piece
Packaging Quantity	1

Additional Product Information

EAN	4019169846134
UPC	804766321924
Commodity Code	84239010
LKZ_FDB/ CatalogID	WT10
Product Group	4913
Group Code	R3P5
Country of origin	China
Compliance with the substance restrictions according to RoHS directive	Since: 02.07.2013
Product class	B: return restricted, please contact your Siemens partner/contact
WEEE (2012/19/EU) Take-Back Obligation	Yes
REACH Art. 33 Duty to inform according to the current list of candidates	

Classifications

	Version	Classification
eClass	6	27-32-03-02
eClass	7.1	27-32-03-02
eClass	8	27-32-03-02
eClass	9	27-32-03-02
eClass	9.1	27-32-03-02
ETIM	5	EC003997
ETIM	8	EC003997
UNSPSC	15	32-15-17-05