

## FEATURES

- Machine screws to DIN85 & DIN963A standards
- Washers to DIN125 standards and nuts to DIN 934 standards
- A4 stainless steel
- Generally non-magnetic
- Cannot be hardened by heat treatment

## 1830 piece Stainless Steel Screw/Bolt Kit, M3, M4, M5, M6

RS Stock No.: 823-875



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

**Product Description**

From the trusted RS PRO brand, this set of high-quality slotted pan and flat machine screws are ideal for many applications. This set also includes washers and nuts in corresponding sizes for the pan head screws.

**General Specifications**


<b>Number Of Pieces</b>	1830
<b>Screw/Bolt Type</b>	Machine Screw
<b>Head Shape</b>	Flat, Pan
<b>Drive Type</b>	Slot
<b>Kit Contents</b>	Slotted Pan M3, Slotted CSK M3, Slotted Pan M4, Slotted CSK M4, Slotted Pan M5, Slotted CSK M5, Slotted Pan M6, Slotted CSK M6
<b>Applications</b>	Chemical equipment, Food & drug production equipment, Bearing plates, Heat Exchanger tubes, Pumps & valves, Underwater installations, Surgical equipment and implants

**Mechanical Specifications**



















<b>Screw/Bolts Lengths</b>	6mm to 40mm
<b>Thread Size</b>	M3, M4, M5, M6
<b>Material</b>	Stainless Steel
<b>Stainless Steel Type</b>	316, A4
<b>Finish</b>	Plain
<b>Screw/Bolt Length Longest</b>	40mm
<b>Screw/Bolt Length Shortest</b>	6mm
<b>Specification</b>	DIN 85, DIN 963A, DIN 934, DIN 125



823-875



- GB** A4 stainless Steel slotted Machine Screw Kit
- D** Sortiment Schlitzkopf-Maschinenschrauben, rostfreier A4-Stahl
- F** Kit de vis à métaux en acier inoxydable A4
- I** Corredo di viti a macchina intagliate in acciaio inossidabile A4
- E** Juego de tornillos para metales de cabeza ranurada de acero inoxidable A4

 M5 x 12 (x20) M5 x 16 (x 12)	 M5 x 25 (x12)	 M4 x 10 (x50) M4 x 16 (x20)	 M4 x 25 (x15)	 M3 x 10 (x40) M3 x 12 (x30)	 M3 x 6 (x40) M3 x 20 (x30)
 M6 x 12 (x10) M6 x 20 (x10) M6 x 25 (x10)	 M5 x 12 (x20) M5 x 20 (x10) M5 x 25 (x15)	 M4 x 12 (x10) M4 x 16 (x10) M4 x 20 (x20)	 M3 x 6 (x60) M3 x 12 (x80) M3 x 20 (x40)	 M6 x 25 (x10)	 M6 x 12 (x15) M6 x 16 (x10)
 M6 (x65)	 M6 (x65)	 M5 (x89)	 M5 (x89)	 M4 (x175)	 M3 (x320)

Kit Contents										
Head Type	Thread Size	L (mm)	Qty	L (mm)	Qty	L (mm)	Qty	L (mm)	Nuts	Washers
Slotted Pan	M3	6	40	10	12	30	20	30	320	385
Slotted CSK	M3	6	60	12	20	40	–	–		n/a
Slotted Pan	M4	10	50	16	25	15	–	–	175	175
Slotted CSK	M4	12	40	16	20	20	–	–		n/a
Slotted Pan	M5	12	20	16	25	10	–	–	89	89
Slotted CSK	M5	12	20	20	25	15	–	–		n/a
Slotted Pan	M6	12	30	16	25	15	–	–	65	65
Slotted CSK	M6	12	10	20	25	10	–	–		n/a