

Features

- **Adjustable Size Range** – Fits gate valve hand wheels from **15 cm to 40 cm** diameter for maximum versatility
- **Durable ABS Construction** – Made from **impact-resistant ABS** plastic to withstand harsh industrial environments.
- **Free-Rotating Design** – Once locked, the unit **rotates freely** to prevent unauthorized operation of the valve.
- **Tool-Free Adjustment** – **Easily clips open and closed** for fast installation and secure fit.
- **Padlock Compatible** – Accommodates **padlocks with up to 9 mm shackle diameter** (sold separately).
- **Reliable Valve Coverage** – Encloses the entire handwheel for effective physical barrier and lockout compliance.

RS PRO Adjustable Gate Valve - Large (For 15 cm to 40 cm Wheel Dia)

RS Stock No.: 0694364



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- *The Adjustable Gate Valve Lockout is a versatile device designed to secure gate valves of various sizes.*
- *This ABS-made lockout device is easy to adjust, covers the valve's wheel, and withstands tough industrial environments.*
- *Adjustable Gate Valve Lockout Device can be easily adjusted to fit gate valves with hand wheel diameters ranging from hand 15 cm to 40 cm.*
- *Once secured, the lockout covers the valve's wheel and rotates freely around it. This prevents unauthorized operation of the valve.*
- *Works in temperatures from -20 °C to 80 °C (-4 °F to 176 °F).*
- *To use, simply clip the two sections apart and fit around the valve. The lockout can be adjusted as needed to fit various valve sizes.*
- *To secure in place, clip the two parts together then attach padlock(s) with upto 9 mm shackle dia (*padlocks sold separately).*

General Specifications

Type	Gate Valve Lockout
Material	ABS
Colour	Red
Package	BOPP + Box

Mechanical Specifications

Minimum Wheel Diameter	15cm
Maximum Wheel Diameter	40cm
Attach padlock(s) with up to	9mm
Weight	1.7 Kgs

Operation Environment Specifications

Withstand temperature	-20°C to 80 °C (-4 °F to 176 °F)
------------------------------	----------------------------------