


NO	DESCRIPTION	DATE
⚠	DEL 222-597	12.28.06'
⚠	∅8.0 → ∅8±0.7 DEL ∅3.3	09.20.07'
⚠	NONE → NICKEL	12.26.12'



P/N: 6539469

APPROVED by _____ DATE: _____

NO	DESCRIPTION	MATERIAL	Q'TY	FINISH
2	NUT	BRASS	2	NICKEL
1	INSULATION	NYLON 66	1	NONE



DESCRIPTION		NYLON SPACER	
製圖	DRAWN <i>Yoko</i>	TOLERANCE .X ±0.2	品名 95-75 ⚠ NICKEL
檢圖	CHECK <i>Angela</i>	.XX ±0.1	單 UNIT mm(in)
認定	APPROVAL <i>Angela</i>	.XXX ±0.05	比例 SCALE 4:1
			DATE 10.25.99'
			版次 A-3
			TITLE ROHS COMPLIANT
			DWG.NO. 95-0072