



## 20482-786 T-shirt

Premium - Modern fit

MASCOT® CROSSOVER



60% organic cotton/40% recycled polyester  
160 g/m<sup>2</sup>



Single jersey fabric. Shrinkage max. 5%. Colour 08: 90% organic cotton/10% viscose.

### Industrial care category C2

### Certifications



### Logo

#### Logo placement:

- T-shirt logo. Mid-chest. Max 32x32 cm/12.5x12.5 inches
- T-shirt logo. Left breast. Max 12x10 cm/4.7x3.9 inches
- T-shirt logo. Right breast. Max 12x10 cm/4.7x3.9 inches
- T-shirt logo. On the back. Max 32x32 cm/12.5x12.5 inches
- T-shirt logo. Mid-nape. Max 12x5 cm/4.7x1.9 inches
- T-shirt logo. Horizontal on right sleeve. Max 10x5 cm/3.9x1.9 inches
- T-shirt logo. Horizontal on left sleeve. Max 10x5 cm/3.9x1.9 inches
- T-shirt logo. Under napeline. Max 12x5 cm/4.7x1.9 inches
- T-shirt logo. Special placement. Contact to discuss further



- The organic cotton is grown without the use of pesticides or chemicals.
- Recycled polyester is made from collected and recycled plastic.
- The fabric dries quickly and retains its colour and shape after every wash.
- The fabric has a high wear resistance and therefore lasts longer overall.

### Technical info

Premium. Modern fit. Round neck. Rib at neck. Neckband.

### User

