

Features

- Excellent molten splash and flame resistance
- Continuous working temperature of 200°C (500°F)
- Superb abrasion and moisture resistance
- Very flexible and available in different colours
- Provides protection from ozone and UV
- Insulates against energy loss in piping and hosing
- Max short time exposure 1650°C (3000°F)
- Available in Red, Black, Yellow, Blue, White and SILVER

RS PRO Fire Sleeve SILVER 5M

RS Stock No.: 0733727



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

RS Pro Fire Sleeve is designed to protect hoses, wires and cables from the hazards of high heat and occasional flame. Made of braided fiberglass yarns in a flexible substrate, it is then coated with high grade silicone rubber. The thick formulation of silicone rubber sheds molten splash, slag, welding splatter, electrical or grinding sparks and contamination. RS Pro Fire Sleeve's key applications are protecting hydraulic hoses, cables and wiring. Used in metallurgy, steel mills, glass works, marine industry and petrochemical industry.

General Specifications

Part Number	Ordering Size (mm)
0730402	4
0730403	6
0731299	8
0731301	10
0731302	12
0731303	14
0731304	16
0731305	19
0731306	22
0731307	25
0731308	28
0731309	32
0731310	35
0731311	38
0733717	41
0733718	51
0733719	57
0733720	63
0733721	70
0733723	76
0733724	83
0733725	89
0733726	95
0733727	102
0733728	114
0733729	127
0733730	140
0733732	168
0733733	180
0733734	203

Approvals

Declarations	Compiles with EN 45545-2 Tested to ISO 11925-2
Standards Met	Meets requirement for IEC 60695-11-10 Classified as HB an V0 Meets requirements for UL94 V0,V1,V2