

Bases with cover H: 100 mm W: 1200 mm



Model	
product brand name	SIVACON S4
product designation	Base
design of the product	height 100 mm
design of cabinet base element	for standard frame
Suitability	
suitability for interaction cable assignment	Yes
suitability for use for outside use	No
Appearance	
RAL color number	sim. RAL 5020
color	blue green basic
product component	module incl. mounting material
• on delivery	
• ventilation	No
Mechanical Design	
height	100 mm
width	1 200 mm
installation width for cabinet installation	1 200 mm
net weight	7.38 kg
material	sheet-steel
material thickness	2.5 mm
Approvals Certificates	
General Product Approval	other



[Miscellaneous](#)



[Miscellaneous](#)

other	Environment
Confirmation	Environmental Con- firmations
	Environmental Con- firmations

Further information
Information on the packaging https://support.industry.siemens.com/cs/ww/en/view/109813875 Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ1012-0BA01>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8PQ1012-0BA01>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ1012-0BA01

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

4/30/2025 

