



Main

Range of product	Acti9
Product or component type	OC or fault contact
Device short name	iOF+SD 24
Signal contacts composition	1 C/O
[In] rated current	2...100 mA at 24 V, DC
9 mm pitches	1

Complementary

Local signalling	Mechanical indicator
Mounting mode	Clip-on
Mounting support	DIN rail
Height	86 mm
Width	9 mm
Depth	71 mm
Net weight	30 g
Colour	White
Connections - terminals	Spring-loaded terminal Ti241 cable(s) 0.5...1.5 mm ² - rigid Spring-loaded terminal Ti241 cable(s) 0.5...1.5 mm ² - flexible
Wire stripping length	10 mm

Environment

Standards	EN/IEC 60947-5-1 EN/IEC 60947-5-4
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins