

M18 BP-O

M18™ PLANER

- Adjustable depth of cut from 0 to 2 mm with twenty locking positions allows the user to accurately set the amount of material to be removed in one pass
- Up to 10.7 mm of rebate depth
- High performance 4-pole motor delivers 14,000 rpm to achieve optimum surface finish
- Faster material removal with two double edged carbide blades over a planning width of 82 mm
- Left or right chip ejection allows the user to keep the chips away from his face when planning
- Extended front shoe allows the tool to be placed on the work piece accurately and quickly
- A kick stand located on the base protects the work piece from accidental damage
- Individual battery cell monitoring optimises tool run time and ensures long term pack durability
- Premium 4-pole brushed motor, REDLITHIUM™ battery pack and REDLINK™ electronic delivering the needed power, run time and durability
- Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™



No load speed (rpm)	14,000
Cutting width (mm)	82
Max. cutting depth (mm)	2
Rebate depth (mm)	10.7
Kit included	No batteries supplied, No charger supplied, No kitbox or bag supplied
Article Number	4933451113