

Features

- Made from Advanced Bio Circular Materials that are more sustainable for the planet future.
- Fully food contact approved to EU10/2011 standards.
- Material Nylon (Polyamide) PA11
- High burst pressure for demanding applications
- Wide operation Temperature Range
- Manufactured in accordance with BS 5409; DIN 73378; DIN 74324 and ISO 7628
- Silicone Free
- Excellent abrasion resistance
- Resistance to wide range of chemicals

RS PRO Air Hoses

RS Stock No.: 0631951



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Food Quality Industrial Nylon tubing made from 98% bio-based material. Ideally suited for application such as Food Production Lines, pneumatics as well as fuel and lubrication applications.

Key Features:

- Made from Advanced Bio Circular Materials that are more sustainable for the planet future.
- Fully food contact approved to EU10/2011 standards.
- High burst pressure for demanding applications
- Wide operation Temperature Range
- Manufactured in accordance with BS 5409; DIN 73378; DIN 74324 and ISO 7628
- Silicone Free
- Excellent abrasion resistance
- Resistance to wide range of chemicals

Applications: • Food Production Line • Pneumatics • Air Brake, fuel and lubrication applications

General Specifications

Manufacturing Series	PA11
Material	Nylon
Colour	Black
Length	30m
Hose Outside Diameter	12 mm
Hose Inside Diameter	9.5 mm
Maximum Operating Pressure	14 Bar
Maximum Operating Temperature	+70°C
Minimum Operating Temperature	-40°C
Application	General Pneumatic Tubing Food Production Line Pneumatics Air Brake, fuel and lubrication applications
Special Features	Light Weight & Durable Over a Wide Temperature Range
Number of Tubes	1
Standards Met	BS 5409; DIN 73378; DIN 74324, ISO 7628