



Lighting **excellence**



@4liteuk



@4liteuk



@4lite




@4liteuk

Torre

Torre IP20 Batten CCT 1800mm
Code: 4L4/2033

Application Commercial, Industrial



Product Features

- Energy-efficient polycarbonate batten
- Ideal for dry storage areas
- 3 CCT selectable between 3000K, 4000K, and 5700K
- BESA fixing points for added convenience and push fit terminals for quick and easy installation
- Slimline design suitable for commercial, industrial, and residential installations
- Adjustable wattage, allowing selection between high or low output
- High efficacy up to 140 lm/W
- 5 year warranty

Technical Information

Wattage	30W/60W
Lumens Delivered	7900lm (60W, 4000K)
Lm/W	141lm/W
Beam Angle	120/100
CRI	80
CCT	3000K/4000K/5700K
Input	220-240V
Operating Temp	-20°C to 40°C
SDCM	6
UGR	30
Cut-Out Size	1228
Product Weight without Packaging	1.577 kg

Technical Information

Light Source	LED
Colour / Finish	White
IP Rating	IP20
Class Protection	1
Internal / External	Internal
Mounting Option	Surface
Lumen Depreciation	L80 55000h
Warranty (Years)	5
CE Mark	Yes