



Main

| | |
|-----------------------------|--|
| Range of product | 9007 |
| Series name | Heavy duty |
| Product or component type | Limit switch lever |
| Device short name | 9007C |
| Associated head | 9007A 9007B 9007C 9007N 9007T10 9007T5 |
| Associated complete product | 9007AW 9007C |
| Movement of operating head | Rotary |
| Type of operator | Cast zinc spring return roller lever length: 0.88 in - offset: - - |
| Type of roller | 1 steel outside roller diameter: 0.63 in - width: 0.25 in |
| Type of approach | Lateral approach |
| Positive opening | Without |

Complementary

| | |
|------------------|------------|
| Switch actuation | By 30° cam |
| Product weight | 0.1 lb(US) |

Environment

| | |
|---------------------------------------|----------------------|
| Ambient air temperature for operation | -20...185 °F |
| Ambient air temperature for storage | -20...185 °F |
| Environmental characteristic | Standard environment |

Offer Sustainability

| | |
|------------------------|--|
| RoHS (date code: YYWW) | Will not be compliant Will not be compliant |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |

| | |
|----------------------------------|---------------------------------------|
| Product environmental profile | Available |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|
