



Oil



Heavy Duty

Oil-repellent nitrile-coated gloves, designed for the safe handling of abrasive materials

- **Enhanced flexibility and durability:** Thanks to a unique nitrile formulation, ActivArm® Hycron 27-602 work gloves are more flexible than PVC-coated gloves and three times as durable as heavy-duty leather alternatives
- **Specialized protection:** These nitrile-coated gloves also provide an excellent barrier to oil and grease, with superb abrasion resistance, making them ideal for handling sharp, abrasive materials
- **Reduced defects risks:** Silicone-free, these ActivArm® gloves are clean and suitable for metalworking and motor manufacture, avoiding any potential contaminant transfer to metal prior to painting
- **Increased comfort:** Their cotton jersey fabric cushions the hand and absorbs perspiration, granting wearers excellent hand protection with breathable comfort



*these abrasion-resistant gloves are three times more durable than standard heavy-duty leather alternatives

Industries

- Automotive
- Machinery and Equipment
- Metal fabrication

Applications

- Handling metal sheets & panels
- Metalworking & assembly operations
- Press injection molding
- Seizing and finishing structural parts
- Fixing, clipping parts and wire harnesses; connecting devices
- Assembly & inspection of components

Key Features

- **Unique nitrile formulation:** Flexibility, durability, abrasion resistance*
- **Cotton jersey liner:** For breathable, comfortable protective gloves
- **Silicone-free design:** Fewer surface defect risks when handling metal

**3x more durability than heavy-duty leather alternatives*

Performance Standards & Regulatory Compliance



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArm® Hycron® 27-602	Finishing: Fully Coated Coating Material: Nitrile Liner Material: Cotton Jersey Cuff Style: Knitwrist		8, 9, 10	246-260 mm/ 9.7-10.23 inches	Blue	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699