

Replacement Light Tower LED, BA15

Distribution by
Rs-online



46-584.1921



<https://rs-online.eao.com/component/46-584.19...>

Your product:



46-584.1921 Replacement Light Tower LED, BA15

OPERATING-/INDICATION PART

Illumination colour: White

ELECTRICAL CHARACTERISTICS

Operating voltage: 24 V AC/DC -20% / +10%

Protection class: II, according to EN / IEC 61140

MECHANICAL CHARACTERISTICS

Weight: 0.007 kg

AMBIENT CONDITION

Operating temperature: - 25 °C ... + 70 °C

CERTIFICATE

Conformities: CE

Standards: EN 55015, EN 61000-3-2, EN 61000-3-3, EN 61547, IEC EN 62471

OTHER

Short Description: Replacement Light Tower LED, BA15, Ø 15 mm x 38 mm, 24 V AC/DC -20% / +10%

Titel Accessory: Replacement Light Tower LED, BA15

Kind of illumination: Single-LED

Dimension: Ø 15 mm x 38 mm

Product attributes: For Signal Light Tower