



S/SC/SOV 104 Multipole Plugs

All dimensions see note 1)




S/SC

SOV



Contact polarity A

Contact polarity Z






CONTACT CONFIGURATION	Contacts	Solder cup \varnothing		Crimp ⁽²⁾ cup \varnothing
104 A Z 051	2	1.86		-
104 A Z 040	3	1.86		1.78
104 A Z 037	4	1.18		1.18
104 A Z 087	4	0.79/2.48		-
104 A Z 053	5	1.18		-

Keying codes (View from F)






Code 1 (-1xx)

Code 2 (-2xx)






Code 3 (-3xx)



Contact configuration for polarity A (View from B)



Contact configuration for polarity Z (View from B)



All dimensions in mm

Rev.

Pages

Notes :

1) All tolerances resulting from connector assembly are typically $\pm 0.3\text{mm}$

2) For optimum crimping refer to available crimping manual.

Part number example : S 104 A092-130+

600011

1c

1/3





www.fischerconnectors.com

S/SC/SOV 104 Multipole Plugs

All dimensions see note 1)



S/SC

SOV



Contact polarity A

Contact polarity Z






CONTACT CONFIGURATION	Contacts	Solder cup \varnothing	Crimp cup ⁽²⁾ \varnothing
104 A Z 065	6	0.79	0.80
104 A Z 054	7	0.79	-
104 A Z 066	8	0.79	0.80
104 A Z 055	9	0.79/1.18	-
104 A Z 056	11	0.79	0.80

Keying codes (View from F)





Code 1 (-1xx)

Code 2 (-2xx)






Code 3 (-3xx)



Contact configuration for polarity A (View from B)



Contact configuration for polarity Z (View from B)



All dimensions in mm

Rev.

Pages

Notes:

1) All tolerances resulting from connector assembly are typically $\pm 0.3\text{mm}$

2) For optimum crimping refer to available crimping manual.

Part number example: S 104 A092-130+

600011

1c

2/3





www.fischerconnectors.com

S/SC/SOV 104 Multipole Plugs

All dimensions see note 1)



S/SC

SOV




Contact polarity A

Contact polarity Z



CONTACT CONFIGURATION	Contacts	Solder cup \varnothing	Crimp cup \varnothing ⁽²⁾
104 A Z 086	16	0.79	0.60
104 A Z 092	19	0.79	0.60
*104 A 124	27	-	0.43

*Please contact us for additional information






Keying codes (View from F)

Code 1 (-1xx)

Code 2 (-2xx)

Code 3 (-3xx)






Contact configuration for polarity A (View from B)



086

092

124



Contact configuration for polarity Z (View from B)



All dimensions in mm

600011

Rev.

1c

Pages

3/3

Notes:

- 1) All tolerances resulting from connector assembly are typically $\pm 0.3\text{mm}$
 - 2) For optimum crimping refer to available crimping manual.
- Part number example : S 104 A092-130+



www.fischerconnectors.com