



Product data sheet

Power tools for trade & industry

Cordless Angle Grinder

PRO GWS 18V-11 S



All-round performer for maximum cutting and grinding versatility

The most important data

Battery voltage	18.0 V
No-load speed	3,000 – 9,000 rpm
Disc diameter	125 mm

Order number 0 601 9N4 000

Technical data

Additional data

Battery voltage	18.0 V
No-load speed	3,000 – 9,000 rpm
Disc diameter	125 mm
X-LOCK	No
BITURBO	No
Grinding spindle thread	M14
Bore size, diameter	22.23 mm
Weight excl. battery	1.7 kg

Noise/vibration information

Surface grinding (roughing)

Uncertainty K	1.5 m/s ²
---------------	----------------------

Sanding with sanding sheet

Uncertainty K	1.5 m/s ²
---------------	----------------------



Product data sheet

Power tools for trade & industry

Advantages:

- Versatile all-rounder with balanced design for wide range of applications
- Excellent durability thanks to 1100 W of power with optimized overload capacity
- Work optimally with many materials due to easy 6-speed selection on dial wheel
- More comfort and less fatigue assured by anti-vibration handle and slimmer grip
- Lower risk of injury while you work thanks to full suite of safety features

**HEAVY
DUTY****PROFESSIONAL
18V
SYSTEM**

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/lb/en/wac/>

