

Datasheet

RS Pro TH200 Nylon Terminal Block Housing IP67, Cable Mount

RS Stock No: **492-4641**



Product Details

RS Pro nylon terminal block housing kit in black colour, accepts all main cables with outer diameter between 6 to 10 mm. It has a base fixing centre of 14.5 mm. The rubber grommets provides either IP54 or IP67 protection.

Features and Benefits

- Rubber grommets provide either IP54 or IP67 protection
- Fixing kit and instructions supplied
- Black plastic housing to UL94 V0



Specifications:

IP Rating	IP67
Material	Nylon
Maximum Operating Temperature	+125°C
Minimum Operating Temperature	-20°C
Mounting Type	Cable Mount
Number of Contacts	3