

Roof plate IP55, W: 1000 mm D: 600 mm



Model	
product brand name	SIVACON S4
product designation	top plate
design of the product	IP55 unventilated
design of the surface	zinc plated
design of the product EMC version	No
Protection class	
protection class IP	IP55
Suitability	
suitability for use for outside use	No
Appearance	
color	miscellaneous
Product details	
product component	
• cable entry	No
• ventilation	No
Mechanical Design	
height	1.5 mm
width	1 000 mm
depth	600 mm
net weight	10 kg
material	sheet-steel
Approvals Certificates	
General Product Approval	other

[Miscellaneous](#)



EG-Konf.



VDE



[Confirmation](#)

Environment

[Environmental Con-
firmations](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging
<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ2301-6BA01>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8PQ2301-6BA01>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ2301-6BA01

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

4/30/2025 

