





Technical data

51208

One direction thrust ball bearings

VISUAL (S)



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	40 mm
D - External diameter	68 mm
T - Thrust bearing height	19 mm
rs - Min fillet radius	1 mm
Mass	0,276 kg

PRODUCT PERFORMANCE

Ca - Dynamic axial load rating	47000000 mN
C0a - Static axial load rating	98500000 mN
Cua - Limit axial load rating	4450000 mN
N lim - Oil lubrication limit speed	23400 °/s
N lim - Grease lubrication limit speed	16200 °/s
Tmin - Min operating temperature	233,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT

Da max - Max shoulder diameter OR	51 mm
da min - Min shoulder diameter IR	57 mm

