



**Profiles:**

**5, Y/6, 8, Z/10, A/13, B/17, 20, C/22, 25, D/32, E/40**

# optibelt VB S=C PLUS

**CLASSICAL V-BELTS**  
**DIN 2215 / ISO 4184**



	<b>5</b>	<b>Y/6</b>	<b>8</b>	<b>Z/10</b>	<b>A/13</b>	<b>B/17</b>	<b>20</b>	<b>C/22</b>	<b>25</b>	<b>D/32</b>	<b>E/40</b>
Nominal length	Inside length $L_i$	Inside length $L_i$	Inside length $L_i$	Inside length $L_i$	Inside length $L_i$	Inside length $L_i$	Inside length $L_i$	Inside length $L_i$	Inside length $L_i$	Inside length $L_i$	Inside length $L_i$
Nominal lengths unit	mm	mm	mm	mm	mm	mm	mm	mm	mm	mm	mm
Height of belt h [mm]	3,00	4,00	5,00	6,00	8,00	11,00	12,50	14,00	16,00	20,00	25,00
Width of belt b [mm]	5,00	6,00	8,00	10,00	13,00	17,00	20,00	22,00	25,00	32,00	40,00
Weight [kg/m]	0,018	0,026	0,042	0,064	0,109	0,196	0,266	0,324	0,420	0,668	0,958
Max. manufacturing length [mm]	-	-	-	4500	10000	21000	21000	21000	21000	21000	21000
Min. pulley diameter [mm]	20,00	28,00	40,00	50,00	71,00	112,00	160,00	180,00	250,00	355,00	500,00
Min. order quantity for non standard lengths from	on request	on request	on request	1800 mm = 20 pieces	1800 mm = 31 pieces	1800 mm = 25 pieces	1800 mm = 21 pieces	1800 mm = 19 pieces	1800 mm = 17 pieces	2000 mm = 11 pieces	3000 mm = 7 pieces
Min. order quantity for non standard lengths from	-	-	-	-	-	2000 mm = 21 pieces	2000 mm = 18 pieces	2000 mm = 16 pieces	2000 mm = 14 pieces	-	-
Min. order quantity for special versions from	-	-	-	1800 mm = 60 pieces	1800 mm = 93 pieces	1800 mm = 75 pieces	1800 mm = 63 pieces	1800 mm = 57 pieces	1800 mm = 51 pieces	2000 mm = 33 pieces	3000 mm = 21 pieces
Min. order quantity for special versions from	-	-	-	-	-	2000 mm = 63 pieces	2000 mm = 54 pieces	2000 mm = 48 pieces	2000 mm = 42 pieces	-	-
Bundle quantity up to 2300 mm	25 pieces	25 pieces	25 pieces	25 pieces	25 pieces	10 pieces	10 pieces	10 pieces	10 pieces	1 piece	-
Bundle quantity up to 5000 mm	-	-	-	10 pieces	10 pieces	10 pieces	5 pieces	5 pieces	5 pieces	1 piece	1 piece
Bundle quantity from 5000 mm	-	-	-	-	10 pieces	5 pieces	3 pieces	3 pieces	3 pieces	1 piece	1 piece

Lengths in bold type are version S=C Plus (SetConstant).

▲ Raw edge, moulded cogged datum length  $L_i$  = pitch length  $L_w$   
Further sizes are available on request

optibelt VB - LC: V-Belts with Light Coloured Cover Fabric  
Profiles: A/13, B/17, 20, C/22, 25, D/32 on request



optibelt LD: Light Duty V-Belts to RMA/MPTA  
Profiles: 2L, 3L, 4L, 5L on request



Ordering example VB: 5 x 190

Description L <sub>i</sub>	Description L <sub>d</sub>	Belt no.	Description L <sub>i</sub>	Description L <sub>d</sub>	Belt no.
<b>5</b>			8 x 1020	8 x 1040	-
5 x 190 ▲	5 x 200	-	8 x 1050	8 x 1070	-
5 x 229 ▲	5 x 239	-	8 x 1075	8 x 1095	-
5 x 260 ▲	5 x 270	-	8 x 1120	8 x 1140	-
5 x 280 ▲	5 x 290	-	8 x 1200	8 x 1220	-
5 x 300 ▲	5 x 310	-	8 x 1250	8 x 1270	-
5 x 315 ▲	5 x 325	-	<b>Z/10</b>		
5 x 322 ▲	5 x 332	-	10 x 290 ▲	10 x 312	Z 11
5 x 335 ▲	5 x 345	-	10 x 315 ▲	10 x 337	Z 12 1/2
5 x 375 ▲	5 x 385	-	10 x 375 ▲	10 x 397	Z 14
5 x 425 ▲	5 x 435	-	10 x 400 ▲	10 x 422	Z 15
5 x 475 ▲	5 x 485	-	10 x 425 ▲	10 x 447	Z 16
5 x 500 ▲	5 x 510	-	10 x 450 ▲	10 x 472	Z 17
5 x 530 ▲	5 x 540	-	10 x 475 ▲	10 x 497	Z 18
5 x 554 ▲	5 x 564	-	10 x 480 ▲	10 x 502	Z 19
5 x 600 ▲	5 x 610	-	10 x 500 ▲	10 x 522	Z 19 3/4
<b>Y/6</b>			10 x 515 ▲	10 x 537	Z 20
6 x 280 ▲	6 x 295	-	10 x 525 ▲	10 x 547	Z 20 1/2
6 x 300 ▲	6 x 315	-	10 x 530 ▲	10 x 552	Z 21
6 x 335 ▲	6 x 350	-	10 x 540 ▲	10 x 562	Z 21 1/4
6 x 400 ▲	6 x 415	-	10 x 560 ▲	10 x 582	Z 22
6 x 425 ▲	6 x 440	-	10 x 575	10 x 597	Z 23
6 x 450 ▲	6 x 465	-	10 x 600	10 x 622	Z 24
6 x 500 ▲	6 x 515	-	10 x 630	10 x 652	Z 25
6 x 540 ▲	6 x 555	-	10 x 650	10 x 672	Z 26
6 x 600 ▲	6 x 615	-	10 x 670	10 x 692	Z 27
6 x 850 ▲	6 x 865	-	10 x 700	10 x 722	Z 27 1/2
<b>8</b>			10 x 710	10 x 732	Z 28
8 x 315 ▲	8 x 335	-	10 x 725	10 x 747	Z 28 1/2
8 x 355 ▲	8 x 375	-	10 x 730	10 x 752	Z 29
8 x 400 ▲	8 x 420	-	10 x 750	10 x 772	Z 29 1/2
8 x 425 ▲	8 x 445	-	10 x 765	10 x 787	Z 30
8 x 450 ▲	8 x 470	-	10 x 775	10 x 797	Z 31
8 x 475 ▲	8 x 495	-	10 x 800	10 x 822	Z 31 1/2
8 x 490 ▲	8 x 510	-	10 x 820	10 x 842	Z 32
8 x 530 ▲	8 x 550	-	10 x 825	10 x 847	Z 33
8 x 560 ▲	8 x 580	-	10 x 850	10 x 872	Z 33 1/2
8 x 575 ▲	8 x 595	-	10 x 865	10 x 887	Z 34
8 x 600 ▲	8 x 620	-	10 x 875	10 x 897	Z 35
8 x 630 ▲	8 x 650	-	10 x 900	10 x 922	Z 36
8 x 670 ▲	8 x 690	-	10 x 925	10 x 947	Z 37
8 x 700 ▲	8 x 720	-	10 x 950	10 x 972	Z 38
8 x 710 ▲	8 x 730	-	10 x 975	10 x 997	Z 38 1/2
8 x 750 ▲	8 x 770	-	10 x 1000	10 x 1022	Z 39
8 x 775 ▲	8 x 795	-	10 x 1016	10 x 1038	Z 40
8 x 800 ▲	8 x 820	-	10 x 1030	10 x 1052	Z 40 1/2
8 x 825	8 x 845	-	10 x 1041	10 x 1063	Z 41
8 x 850	8 x 870	-	10 x 1050	10 x 1072	Z 41 1/2
8 x 875	8 x 895	-	10 x 1060	10 x 1082	Z 42
8 x 900	8 x 920	-	10 x 1080	10 x 1102	Z 43
8 x 950	8 x 970	-	10 x 1100	10 x 1122	Z 43 1/4
8 x 1000	8 x 1020	-	10 x 1120	10 x 1142	Z 44

Description L <sub>i</sub>	Description L <sub>d</sub>	Belt no.	Description L <sub>i</sub>	Description L <sub>d</sub>	Belt no.
10 x 1150	10 x 1172	Z 45	13 x 710	13 x 740	A 28
10 x 1165	10 x 1187	Z 46	13 x 730	13 x 760	A 29
10 x 1180	10 x 1202	Z 46 1/2	13 x 750	13 x 780	A 29 1/2
10 x 1194	10 x 1216	Z 47	13 x 767	13 x 797	A 30
10 x 1215	10 x 1237	Z 48	13 x 775	13 x 805	A 31
10 x 1225	10 x 1247	Z 48 1/2	13 x 800	13 x 830	A 31 1/2
10 x 1250	10 x 1272	Z 49	13 x 813	13 x 843	A 32
10 x 1270	10 x 1292	Z 50	13 x 825	13 x 855	A 32 1/2
10 x 1295	10 x 1317	Z 51	13 x 841	13 x 871	A 33
10 x 1320	10 x 1342	Z 52	13 x 850	13 x 880	A 34
10 x 1346	10 x 1368	Z 53	13 x 875	13 x 905	A 34 1/2
10 x 1371	10 x 1393	Z 54	13 x 889	13 x 919	A 35
10 x 1400	10 x 1422	Z 55	13 x 900	13 x 930	A 35 1/2
10 x 1422	10 x 1444	Z 56	13 x 914	13 x 944	A 36
10 x 1450	10 x 1472	Z 57	13 x 925	13 x 955	A 37
10 x 1475	10 x 1497	Z 58	13 x 950	13 x 980	A 37 1/2
10 x 1500	10 x 1522	Z 59	13 x 965	13 x 995	A 38
10 x 1524	10 x 1546	Z 60	13 x 975	13 x 1005	A 38 1/2
<b>10 x 1550</b>	10 x 1572	Z 61	13 x 1000	13 x 1030	A 39
<b>10 x 1575</b>	10 x 1597	Z 62	13 x 1016	13 x 1046	A 40
<b>10 x 1600</b>	10 x 1622	Z 63	13 x 1030	13 x 1060	A 40 1/2
<b>10 x 1626</b>	10 x 1648	Z 64	13 x 1041	13 x 1071	A 41
<b>10 x 1651</b>	10 x 1673	Z 65	13 x 1050	13 x 1080	A 41 1/2
<b>10 x 1675</b>	10 x 1697	Z 66	13 x 1060	13 x 1090	A 42
<b>10 x 1700</b>	10 x 1722	Z 67	13 x 1075	13 x 1105	A 42 1/2
<b>10 x 1725</b>	10 x 1747	Z 68	13 x 1100	13 x 1130	A 43
<b>10 x 1750</b>	10 x 1772	Z 69	13 x 1105	13 x 1135	A 43 1/2
<b>10 x 1775</b>	10 x 1797	Z 70	13 x 1120	13 x 1150	A 44
<b>10 x 1800</b>	10 x 1822	Z 71	13 x 1143	13 x 1173	A 45
<b>10 x 1850</b>	10 x 1872	Z 73	13 x 1150	13 x 1180	A 45 1/2
<b>10 x 1900</b>	10 x 1922	Z 75	<b>13 x 1168</b>	13 x 1198	A 46
<b>10 x 1975</b>	10 x 1997	Z 78	<b>13 x 1180</b>	13 x 1210	A 46 1/2
<b>10 x 2000</b>	10 x 2022	Z 79	<b>13 x 1200</b>	13 x 1230	A 47
<b>10 x 2120</b>	10 x 2142	Z 83 1/2	<b>13 x 1215</b>	13 x 1245	A 47 1/2
<b>10 x 2240</b>	10 x 2262	Z 88	<b>13 x 1220</b>	13 x 1250	A 48
<b>10 x 2360</b>	10 x 2382	Z 93	<b>13 x 1225</b>	13 x 1255	A 48 1/2
<b>10 x 2500</b>	10 x 2522	Z 98	<b>13 x 1250</b>	13 x 1280	A 49
<b>A/13</b>			<b>13 x 1270</b>	13 x 1300	A 50
13 x 407	13 x 437	A 16	<b>13 x 1300</b>	13 x 1330	A 51
13 x 457	13 x 487	A 18	<b>13 x 1320</b>	13 x 1350	A 52
13 x 480	13 x 510	A 19	<b>13 x 1350</b>	13 x 1380	A 53
13 x 508	13 x 538	A 20	<b>13 x 1375</b>	13 x 1405	A 54
13 x 535	13 x 565	A 21	<b>13 x 1400</b>	13 x 1430	A 55
13 x 560	13 x 590	A 22	<b>13 x 1422</b>	13 x 1452	A 56
13 x 575	13 x 605	A 23	<b>13 x 1450</b>	13 x 1480	A 57
13 x 600	13 x 630	A 23 1/2	<b>13 x 1475</b>	13 x 1505	A 58
13 x 610	13 x 640	A 24	<b>13 x 1500</b>	13 x 1530	A 59
13 x 630	13 x 660	A 25	<b>13 x 1525</b>	13 x 1555	A 60
13 x 650	13 x 680	A 26	<b>13 x 1550</b>	13 x 1580	A 61
13 x 670	13 x 700	A 26 1/2	<b>13 x 1575</b>	13 x 1605	A 62
13 x 686	13 x 716	A 27	<b>13 x 1600</b>	13 x 1630	A 63
13 x 700	13 x 730	A 27 1/2	<b>13 x 1625</b>	13 x 1655	A 64

Description L <sub>1</sub>	Description L <sub>d</sub>	Belt no.	Description L <sub>1</sub>	Description L <sub>d</sub>	Belt no.
<b>13 x 1650</b>	13 x 1680	A 65	<b>13 x 3454</b>	13 x 3484	A 136
<b>13 x 1676</b>	13 x 1706	A 66	<b>13 x 3550</b>	13 x 3580	A 140
<b>13 x 1700</b>	13 x 1730	A 67	<b>13 x 3658</b>	13 x 3688	A 144
<b>13 x 1725</b>	13 x 1755	A 68	<b>13 x 3750</b>	13 x 3780	A 148
<b>13 x 1750</b>	13 x 1780	A 69	<b>13 x 4000</b>	13 x 4030	A 158
<b>13 x 1775</b>	13 x 1805	A 70	<b>13 x 4250</b>	13 x 4280	A 167
<b>13 x 1800</b>	13 x 1830	A 71	<b>13 x 4750</b>	13 x 4780	A 187
<b>13 x 1825</b>	13 x 1855	A 72	<b>13 x 5000</b>	13 x 5030	A 197
<b>13 x 1854</b>	13 x 1884	A 73	<b>B/17</b>		
<b>13 x 1880</b>	13 x 1910	A 74	17 x 570	17 x 610	B 23
<b>13 x 1900</b>	13 x 1930	A 75	17 x 615	17 x 655	B 24
<b>13 x 1930</b>	13 x 1960	A 76	17 x 630	17 x 670	B 25
<b>13 x 1956</b>	13 x 1986	A 77	17 x 650	17 x 690	B 26
<b>13 x 1980</b>	13 x 2010	A 78	17 x 670	17 x 710	B 26 1/2
<b>13 x 2000</b>	13 x 2030	A 79	17 x 686	17 x 726	B 27
<b>13 x 2032</b>	13 x 2062	A 80	17 x 710	17 x 750	B 28
<b>13 x 2060</b>	13 x 2090	A 81	17 x 725	17 x 765	B 29
<b>13 x 2083</b>	13 x 2113	A 82	17 x 750	17 x 790	B 30
<b>13 x 2100</b>	13 x 2130	A 83	17 x 775	17 x 815	B 31
<b>13 x 2120</b>	13 x 2150	A 83 1/2	17 x 800	17 x 840	B 32
<b>13 x 2134</b>	13 x 2164	A 84	17 x 825	17 x 865	B 32 1/2
<b>13 x 2150</b>	13 x 2180	A 84 1/2	17 x 836	17 x 876	B 33
<b>13 x 2160</b>	13 x 2190	A 85	17 x 850	17 x 890	B 34
<b>13 x 2185</b>	13 x 2190	A 86	17 x 875	17 x 915	B 34 1/2
<b>13 x 2200</b>	13 x 2230	A 86 1/2	17 x 889	17 x 929	B 35
<b>13 x 2210</b>	13 x 2240	A 87	17 x 900	17 x 940	B 36
<b>13 x 2240</b>	13 x 2270	A 88	17 x 925	17 x 965	B 37
<b>13 x 2261</b>	13 x 2291	A 89	17 x 950	17 x 990	B 37 1/2
<b>13 x 2286</b>	13 x 2316	A 90	17 x 965	17 x 1005	B 38
<b>13 x 2311</b>	13 x 2341	A 91	17 x 975	17 x 1015	B 38 1/2
<b>13 x 2337</b>	13 x 2367	A 92	17 x 1000	17 x 1040	B 39
<b>13 x 2360</b>	13 x 2390	A 93	17 x 1016	17 x 1056	B 40
<b>13 x 2388</b>	13 x 2418	A 94	17 x 1030	17 x 1070	B 40 1/2
<b>13 x 2413</b>	13 x 2443	A 95	17 x 1040	17 x 1080	B 41
<b>13 x 2438</b>	13 x 2468	A 96	17 x 1050	17 x 1090	B 41 1/2
<b>13 x 2464</b>	13 x 2494	A 97	17 x 1060	17 x 1100	B 42
<b>13 x 2500</b>	13 x 2530	A 98	17 x 1075	17 x 1115	B 42 1/2
<b>13 x 2540</b>	13 x 2570	A 100	17 x 1090	17 x 1130	B 43
<b>13 x 2591</b>	13 x 2621	A 102	17 x 1100	17 x 1140	B 43 1/4
<b>13 x 2650</b>	13 x 2680	A 104	17 x 1120	17 x 1160	B 44
<b>13 x 2667</b>	13 x 2697	A 105	17 x 1150	17 x 1190	B 45
<b>13 x 2725</b>	13 x 2755	A 107	17 x 1163	17 x 1203	B 45 1/2
<b>13 x 2743</b>	13 x 2773	A 108	<b>17 x 1175</b>	17 x 1215	B 46
<b>13 x 2800</b>	13 x 2830	A 110	<b>17 x 1180</b>	17 x 1220	B 46 1/2
<b>13 x 2845</b>	13 x 2875	A 112	<b>17 x 1200</b>	17 x 1240	B 47
<b>13 x 2896</b>	13 x 2926	A 114	<b>17 x 1215</b>	17 x 1255	B 48
<b>13 x 2946</b>	13 x 2976	A 116	<b>17 x 1225</b>	17 x 1265	B 48 1/2
<b>13 x 3000</b>	13 x 3030	A 118	<b>17 x 1250</b>	17 x 1290	B 49
<b>13 x 3048</b>	13 x 3078	A 120	<b>17 x 1275</b>	17 x 1315	B 50
<b>13 x 3150</b>	13 x 3180	A 124	<b>17 x 1300</b>	17 x 1340	B 51
<b>13 x 3250</b>	13 x 3280	A 128	<b>17 x 1320</b>	17 x 1360	B 52
<b>13 x 3350</b>	13 x 3380	A 132	<b>17 x 1335</b>	17 x 1375	B 52 1/2

Description L <sub>i</sub>	Description L <sub>d</sub>	Belt no.	Description L <sub>i</sub>	Description L <sub>d</sub>	Belt no.
<b>17 x 1350</b>	17 x 1390	B 53	<b>17 x 2540</b>	17 x 2580	B 100
<b>17 x 1360</b>	17 x 1400	B 53 1/2	<b>17 x 2565</b>	17 x 2605	B 101
<b>17 x 1372</b>	17 x 1412	B 54	<b>17 x 2600</b>	17 x 2640	B 102
<b>17 x 1400</b>	17 x 1440	B 55	<b>17 x 2616</b>	17 x 2656	B 103
<b>17 x 1422</b>	17 x 1462	B 56	<b>17 x 2650</b>	17 x 2690	B 104
<b>17 x 1450</b>	17 x 1490	B 57	<b>17 x 2667</b>	17 x 2707	B 105
<b>17 x 1473</b>	17 x 1513	B 58	<b>17 x 2700</b>	17 x 2740	B 106
<b>17 x 1500</b>	17 x 1540	B 59	<b>17 x 2718</b>	17 x 2758	B 107
<b>17 x 1525</b>	17 x 1565	B 60	<b>17 x 2750</b>	17 x 2790	B 108
<b>17 x 1550</b>	17 x 1590	B 61	<b>17 x 2800</b>	17 x 2840	B 110
<b>17 x 1575</b>	17 x 1615	B 62	<b>17 x 2845</b>	17 x 2885	B 112
<b>17 x 1600</b>	17 x 1640	B 63	<b>17 x 2900</b>	17 x 2940	B 114
<b>17 x 1625</b>	17 x 1665	B 64	<b>17 x 2921</b>	17 x 2961	B 115
<b>17 x 1650</b>	17 x 1690	B 65	<b>17 x 2950</b>	17 x 2990	B 116
<b>17 x 1676</b>	17 x 1716	B 66	<b>17 x 3000</b>	17 x 3040	B 118
<b>17 x 1700</b>	17 x 1740	B 67	<b>17 x 3048</b>	17 x 3088	B 120
<b>17 x 1725</b>	17 x 1765	B 68	<b>17 x 3099</b>	17 x 3139	B 122
<b>17 x 1750</b>	17 x 1790	B 69	<b>17 x 3150</b>	17 x 3190	B 124
<b>17 x 1761</b>	17 x 1801	B 69 1/2	<b>17 x 3200</b>	17 x 3240	B 126
<b>17 x 1775</b>	17 x 1815	B 70	<b>17 x 3250</b>	17 x 3290	B 128
<b>17 x 1800</b>	17 x 1840	B 71	<b>17 x 3302</b>	17 x 3342	B 130
<b>17 x 1829</b>	17 x 1869	B 72	<b>17 x 3350</b>	17 x 3390	B 132
<b>17 x 1850</b>	17 x 1890	B 73	<b>17 x 3404</b>	17 x 3444	B 134
<b>17 x 1880</b>	17 x 1920	B 74	<b>17 x 3450</b>	17 x 3490	B 136
<b>17 x 1900</b>	17 x 1940	B 75	<b>17 x 3505</b>	17 x 3545	B 138
<b>17 x 1930</b>	17 x 1970	B 76	<b>17 x 3550</b>	17 x 3590	B 140
<b>17 x 1950</b>	17 x 1990	B 77	<b>17 x 3600</b>	17 x 3640	B 142
<b>17 x 1981</b>	17 x 2021	B 78	<b>17 x 3658</b>	17 x 3698	B 144
<b>17 x 2000</b>	17 x 2040	B 79	<b>17 x 3700</b>	17 x 3740	B 146
<b>17 x 2032</b>	17 x 2072	B 80	<b>17 x 3750</b>	17 x 3790	B 148
<b>17 x 2060</b>	17 x 2100	B 81	<b>17 x 3810</b>	17 x 3850	B 150
<b>17 x 2083</b>	17 x 2123	B 82	<b>17 x 3850</b>	17 x 3890	B 151
<b>17 x 2100</b>	17 x 2140	B 83	<b>17 x 3861</b>	17 x 3901	B 152
<b>17 x 2120</b>	17 x 2160	B 83 1/2	<b>17 x 3912</b>	17 x 3952	B 154
<b>17 x 2134</b>	17 x 2174	B 84	<b>17 x 3950</b>	17 x 3990	B 155
<b>17 x 2160</b>	17 x 2200	B 85	<b>17 x 3962</b>	17 x 4002	B 156
<b>17 x 2200</b>	17 x 2240	B 86	<b>17 x 4000</b>	17 x 4040	B 158
<b>17 x 2210</b>	17 x 2250	B 87	<b>17 x 4064</b>	17 x 4104	B 160
<b>17 x 2240</b>	17 x 2280	B 88	<b>17 x 4115</b>	17 x 4155	B 162
<b>17 x 2261</b>	17 x 2301	B 89	<b>17 x 4200</b>	17 x 4240	B 165
<b>17 x 2286</b>	17 x 2326	B 90	<b>17 x 4250</b>	17 x 4290	B 167
<b>17 x 2300</b>	17 x 2340	B 91	<b>17 x 4394</b>	17 x 4434	B 173
<b>17 x 2337</b>	17 x 2377	B 92	<b>17 x 4450</b>	17 x 4490	B 175
<b>17 x 2360</b>	17 x 2400	B 93	<b>17 x 4500</b>	17 x 4540	B 177
<b>17 x 2388</b>	17 x 2428	B 94	<b>17 x 4572</b>	17 x 4612	B 180
<b>17 x 2400</b>	17 x 2440	B 94 1/2	<b>17 x 4750</b>	17 x 4790	B 187
<b>17 x 2413</b>	17 x 2453	B 95	<b>17 x 4953</b>	17 x 4993	B 195
<b>17 x 2438</b>	17 x 2478	B 96	<b>17 x 5000</b>	17 x 5040	B 197
<b>17 x 2450</b>	17 x 2490	B 96 1/2	<b>17 x 5300</b>	17 x 5340	B 208
<b>17 x 2465</b>	17 x 2505	B 97	<b>17 x 5334</b>	17 x 5374	B 210
<b>17 x 2500</b>	17 x 2540	B 98	<b>17 x 5600</b>	17 x 5640	B 220
<b>17 x 2515</b>	17 x 2555	B 99	<b>17 x 6000</b>	17 x 6040	B 236

Description L <sub>i</sub>	Description L <sub>d</sub>	Belt no.	Description L <sub>i</sub>	Description L <sub>d</sub>	Belt no.
<b>17 x 6096</b>	17 x 6136	B 240	<b>22 x 1650</b>	22 x 1708	C 65
<b>17 x 6300</b>	17 x 6340	B 248	<b>22 x 1676</b>	22 x 1734	C 66
<b>17 x 6700</b>	17 x 6740	B 264	<b>22 x 1700</b>	22 x 1758	C 67
<b>17 x 7000</b>	17 x 7040	B 276	<b>22 x 1727</b>	22 x 1785	C 68
<b>17 x 7100</b>	17 x 7140	B 280	<b>22 x 1750</b>	22 x 1808	C 69
<b>20</b>					
20 x 900	20 x 950	-	<b>22 x 1778</b>	22 x 1836	C 70
20 x 1000	20 x 1050	-	<b>22 x 1800</b>	22 x 1858	C 71
20 x 1120	20 x 1170	-	<b>22 x 1829</b>	22 x 1887	C 72
20 x 1180	20 x 1230	-	<b>22 x 1829</b>	22 x 1887	C 72
<b>20 x 1250</b>	20 x 1300	-	<b>22 x 1854</b>	22 x 1912	C 73
<b>20 x 1320</b>	20 x 1370	-	<b>22 x 1880</b>	22 x 1938	C 74
<b>20 x 1400</b>	20 x 1450	-	<b>22 x 1900</b>	22 x 1958	C 75
<b>20 x 1500</b>	20 x 1550	-	<b>22 x 1930</b>	22 x 1988	C 76
<b>20 x 1600</b>	20 x 1650	-	<b>22 x 1956</b>	22 x 2014	C 77
<b>20 x 1700</b>	20 x 1750	-	<b>22 x 1981</b>	22 x 2039	C 78
<b>20 x 1800</b>	20 x 1850	-	<b>22 x 2000</b>	22 x 2058	C 79
<b>20 x 1900</b>	20 x 1950	-	<b>22 x 2032</b>	22 x 2090	C 80
<b>20 x 2000</b>	20 x 2050	-	<b>22 x 2060</b>	22 x 2118	C 81
<b>20 x 2120</b>	20 x 2170	-	<b>22 x 2083</b>	22 x 2141	C 82
<b>20 x 2240</b>	20 x 2290	-	<b>22 x 2108</b>	22 x 2166	C 83
<b>20 x 2360</b>	20 x 2410	-	<b>22 x 2120</b>	22 x 2178	C 83 1/2
<b>20 x 2500</b>	20 x 2550	-	<b>22 x 2134</b>	22 x 2192	C 84
<b>20 x 2650</b>	20 x 2700	-	<b>22 x 2159</b>	22 x 2217	C 85
<b>20 x 2800</b>	20 x 2850	-	<b>22 x 2184</b>	22 x 2242	C 86
<b>20 x 3000</b>	20 x 3050	-	<b>22 x 2210</b>	22 x 2268	C 87
<b>20 x 3150</b>	20 x 3200	-	<b>22 x 2240</b>	22 x 2298	C 88
<b>20 x 3350</b>	20 x 3400	-	<b>22 x 2261</b>	22 x 2319	C 89
<b>20 x 3550</b>	20 x 3600	-	<b>22 x 2286</b>	22 x 2344	C 90
<b>20 x 3750</b>	20 x 3800	-	<b>22 x 2337</b>	22 x 2395	C 92
<b>20 x 4000</b>	20 x 4050	-	<b>22 x 2360</b>	22 x 2418	C 93
<b>20 x 4500</b>	20 x 4550	-	<b>22 x 2388</b>	22 x 2446	C 94
<b>20 x 5000</b>	20 x 5050	-	<b>22 x 2413</b>	22 x 2471	C 95
<b>20 x 6000</b>	20 x 6050	-	<b>22 x 2438</b>	22 x 2496	C 96
<b>C/22</b>					
22 x 1090	22 x 1148	C 43	<b>22 x 2450</b>	22 x 2508	C 96 1/2
<b>22 x 1200</b>	22 x 1258	C 47	<b>22 x 2464</b>	22 x 2522	C 97
<b>22 x 1215</b>	22 x 1273	C 48	<b>22 x 2500</b>	22 x 2558	C 98
<b>22 x 1250</b>	22 x 1308	C 49	<b>22 x 2525</b>	22 x 2583	C 99
<b>22 x 1295</b>	22 x 1353	C 51	<b>22 x 2540</b>	22 x 2598	C 100
<b>22 x 1320</b>	22 x 1378	C 52	<b>22 x 2560</b>	22 x 2618	C 101
<b>22 x 1350</b>	22 x 1408	C 53	<b>22 x 2591</b>	22 x 2649	C 102
<b>22 x 1375</b>	22 x 1433	C 54	<b>22 x 2642</b>	22 x 2700	C 104
<b>22 x 1400</b>	22 x 1458	C 55	<b>22 x 2667</b>	22 x 2725	C 105
<b>22 x 1425</b>	22 x 1483	C 56	<b>22 x 2692</b>	22 x 2750	C 106
<b>22 x 1450</b>	22 x 1508	C 57	<b>22 x 2750</b>	22 x 2808	C 108
<b>22 x 1475</b>	22 x 1533	C 58	<b>22 x 2800</b>	22 x 2858	C 110
<b>22 x 1500</b>	22 x 1558	C 59	<b>22 x 2845</b>	22 x 2903	C 112
<b>22 x 1524</b>	22 x 1582	C 60	<b>22 x 2896</b>	22 x 2954	C 114
<b>22 x 1550</b>	22 x 1608	C 61	<b>22 x 2921</b>	22 x 2979	C 115
<b>22 x 1574</b>	22 x 1632	C 62	<b>22 x 2950</b>	22 x 3008	C 116
<b>22 x 1600</b>	22 x 1658	C 63	<b>22 x 2965</b>	22 x 3023	C 117
			<b>22 x 3000</b>	22 x 3058	C 118
			<b>22 x 3048</b>	22 x 3106	C 120

Description L <sub>1</sub>	Description L <sub>d</sub>	Belt no.	Description L <sub>1</sub>	Description L <sub>d</sub>	Belt no.
<b>22 x 3099</b>	22 x 3157	C 122	<b>25 x 2360</b>	25 x 2420	-
<b>22 x 3150</b>	22 x 3208	C 124	<b>25 x 2500</b>	25 x 2560	-
<b>22 x 3200</b>	22 x 3258	C 126	<b>25 x 2650</b>	25 x 2710	-
<b>22 x 3250</b>	22 x 3308	C 128	<b>25 x 2700</b>	25 x 2760	-
<b>22 x 3302</b>	22 x 3360	C 130	<b>25 x 2800</b>	25 x 2860	-
<b>22 x 3350</b>	22 x 3408	C 132	<b>25 x 3000</b>	25 x 3060	-
<b>22 x 3404</b>	22 x 3462	C 134	<b>25 x 3150</b>	25 x 3210	-
<b>22 x 3450</b>	22 x 3508	C 136	<b>25 x 3350</b>	25 x 3410	-
<b>22 x 3505</b>	22 x 3563	C 138	<b>25 x 3550</b>	25 x 3610	-
<b>22 x 3550</b>	22 x 3608	C 140	<b>25 x 3750</b>	25 x 3810	-
<b>22 x 3607</b>	22 x 3665	C 142	<b>25 x 4000</b>	25 x 4060	-
<b>22 x 3658</b>	22 x 3716	C 144	<b>25 x 4250</b>	25 x 4310	-
<b>22 x 3700</b>	22 x 3758	C 146	<b>25 x 4500</b>	25 x 4560	-
<b>22 x 3750</b>	22 x 3808	C 148	<b>25 x 4750</b>	25 x 4810	-
<b>22 x 3810</b>	22 x 3868	C 150	<b>25 x 5000</b>	25 x 5060	-
<b>22 x 4000</b>	22 x 4058	C 158	<b>25 x 5300</b>	25 x 5360	-
<b>22 x 4100</b>	22 x 4158	C 162	<b>25 x 5600</b>	25 x 5660	-
<b>22 x 4216</b>	22 x 4274	C 166	<b>25 x 6000</b>	25 x 6060	-
<b>22 x 4250</b>	22 x 4308	C 167	<b>25 x 6300</b>	25 x 6360	-
<b>22 x 4267</b>	22 x 4325	C 168	<b>25 x 6700</b>	25 x 6760	-
<b>22 x 4318</b>	22 x 4376	C 170	<b>25 x 7100</b>	25 x 7160	-
<b>22 x 4394</b>	22 x 4452	C 173	<b>25 x 7500</b>	25 x 7560	-
<b>22 x 4445</b>	22 x 4503	C 175	<b>25 x 8000</b>	25 x 8060	-
<b>22 x 4500</b>	22 x 4558	C 177	<b>25 x 8500</b>	25 x 8560	-
<b>22 x 4572</b>	22 x 4630	C 180	<b>25 x 9000</b>	25 x 9060	-
<b>22 x 4750</b>	22 x 4808	C 187	<b>D/32</b>		
<b>22 x 4826</b>	22 x 4884	C 190	<b>32 x 2000</b>	32 x 2075	D 79
<b>22 x 4953</b>	22 x 5011	C 195	<b>32 x 2500</b>	32 x 2575	D 98
<b>22 x 5000</b>	22 x 5058	C 197	<b>32 x 2650</b>	32 x 2725	D 104
<b>22 x 5330</b>	22 x 5358	C 208	<b>32 x 2800</b>	32 x 2875	D 110
<b>22 x 5334</b>	22 x 5392	C 210	<b>32 x 3000</b>	32 x 3075	D 118
<b>22 x 5600</b>	22 x 5658	C 220	<b>32 x 3048</b>	32 x 3123	D 120
<b>22 x 5715</b>	22 x 5773	C 225	<b>32 x 3150</b>	32 x 3225	D 124
<b>22 x 6000</b>	22 x 6058	C 236	<b>32 x 3251</b>	32 x 3326	D 128
<b>22 x 6096</b>	22 x 6154	C 240	<b>32 x 3350</b>	32 x 3425	D 132
<b>22 x 6300</b>	22 x 6358	C 248	<b>32 x 3425</b>	32 x 3500	D 135
<b>22 x 6700</b>	22 x 6758	C 264	<b>32 x 3454</b>	32 x 3529	D 136
<b>22 x 6858</b>	22 x 6916	C 270	<b>32 x 3550</b>	32 x 3625	D 140
<b>22 x 7100</b>	22 x 7158	C 280	<b>32 x 3658</b>	32 x 3733	D 144
<b>22 x 7500</b>	22 x 7558	C 295	<b>32 x 3750</b>	32 x 3825	D 148
<b>22 x 7620</b>	22 x 7678	C 300	<b>32 x 3925</b>	32 x 4000	D 154
<b>22 x 8000</b>	22 x 8058	C 315	<b>32 x 4000</b>	32 x 4075	D 158
<b>25</b>			<b>32 x 4115</b>	32 x 4190	D 162
<b>25 x 1400</b>	25 x 1460	-	<b>32 x 4250</b>	32 x 4325	D 167
<b>25 x 1500</b>	25 x 1560	-	<b>32 x 4394</b>	32 x 4469	D 173
<b>25 x 1600</b>	25 x 1660	-	<b>32 x 4500</b>	32 x 4575	D 177
<b>25 x 1700</b>	25 x 1760	-	<b>32 x 4572</b>	32 x 4647	D 180
<b>25 x 1800</b>	25 x 1860	-	<b>32 x 4750</b>	32 x 4825	D 187
<b>25 x 1900</b>	25 x 1960	-	<b>32 x 4953</b>	32 x 5028	D 195
<b>25 x 2000</b>	25 x 2060	-	<b>32 x 5000</b>	32 x 5075	D 197
<b>25 x 2120</b>	25 x 2180	-	<b>32 x 5300</b>	32 x 5375	D 208
<b>25 x 2240</b>	25 x 2300	-	<b>32 x 5334</b>	32 x 5409	D 210

