
# RS PRO Non-Metallic Blind Flange Lockout - Extra Small (Pipe Size 1-1/2 - 5-5/8)

RS Stock No.: 0802206



## Features

- Adjustable blind flange lockout device.
- Prevents removal of pipe blinds during maintenance.
- Conceals and locks access to flange nuts.
- Durable high-impact plastic construction.
- Accepts padlocks up to 8 mm shackle diameter.
- Suitable for –20°C to +60°C environments.
- Ideal for oil & gas, petrochemical, and process industries.

RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

- ***Prevents Unintentional Removal of Pipe Blinds*** *- Specifically engineered to secure blind flanges and prevent unauthorised or accidental removal during maintenance or shutdown procedures.*
- ***Adjustable Secure-Fit Design*** *- Adjustable configuration ensures a tight and secure fit over flange nuts, fully concealing and restricting access to the fastening hardware.*
- ***Conceals & Locks Flange Nuts*** *- Encloses the nuts holding the blind flange in place, preventing tampering and maintaining isolation integrity.*
- ***High-Impact Durable Plastic Construction*** *- Manufactured from strong, impact-resistant plastic designed to withstand harsh industrial environments.*
- ***Wide Operating Temperature Range*** *- Suitable for use in temperatures from* ***-20°C to +60°C****, making it ideal for both indoor and outdoor applications.*
- ***Padlock Compatible*** *- Accommodates padlocks with shackle diameters up to* ***8 mm****, allowing secure lockout control.*

## General Specifications

| | |
|---|---|
| **Type** | Blind Flange Lockout |
| **Material** | PVC |
| **Colour** | Red |
| **Padlock holes** | 01 |
| **Package** | PE-LD |

## Mechanical Specifications

| | |
|---|---|
| **Fits Nut Diameter (Class 150)** | 0.75" to 0.88" (19.05mm – 22.35mm) |
| **Fits Nut Diameter (Class 300)** | 0.75" to 1.00" (19.05mm –25.4mm) |
| **Pipe Flange Width Range** | 1-1/2" - 5-5/8" (38.1.3mm - 142.88mm) |
| **Length** | 170mm |
| **Width** | 40mm |
| **Height** | 85mm |
| **Weight** | 58 Grams |

## Operation Environment Specifications

| | |
|---|---|
| **Withstand temperature** | -20°C to +60°C |


DANGER
LOCKED
OUT
DO NOT REMOVE
DO NOT
OPERATE