

S170 - Hi-Vis Cotton Comfort T-Shirt S/S

Collection: Cotton Comfort™

Range: High Visibility

Shell Fabric: 55% Cotton, 45% Polyester, Knit, 175g

Outer Carton: 48

Product information

Using our Cotton Comfort fabric which is lightweight and breathable, this short sleeve t-shirt has a taped neck seam for extra comfort and uses reflective tape for enhanced visibility.

Cotton Comfort™

Cotton Comfort™ fabric is manufactured from a cotton rich fabric with cotton on the inside for comfort and polyester on the outside for maximum durability. The cotton polyester mix ensures that the fabric is highly breathable and that a comfortable temperature is maintained at all times.

High Visibility

Our extensive range of High-Visibility clothing meets stringent requirements in both design and construction, to ensure compliance with the latest EN ISO 20471 & ANSI standards. Innovative and technical, our High Visibility range is ideal for those who will not compromise on style, comfort, protection and performance.

Standards

EN ISO 20471 Class 2

RIS 3279 TOM Issue 2 (Orange Only)

ANSI/ISEA 107 Type R Class 2

ANSI/ISEA 107 TYPE P Class 3



Features

- Moisture wicking fabric helping to keep the body cool and dry
- High cotton content for superior comfort
- Crew neck
- Taped neck seam for extra comfort
- Lightweight and comfortable
- Designed with a comfort fit
- Reflective tape for increased visibility
- 40+ UPF rated fabric to block 98% of UV rays
- Certified to EN ISO 20471 after 50x washes
- Complies with RIS 3279-TOM for rail industry (orange only)
- CE certified

S170 - Hi-Vis Cotton Comfort T-Shirt S/S
Commodity Code: 6109100010

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
 Bracetown Business Park
 D15 YN2P, Ireland
 Cert No: 2777/13374-02/E00-00

SATRA Technology Centre Ltd (Notified Body No.: AB: 0321)
 SATRA Technology Park
 NN16 8SD, United Kingdom
 Cert No: AB0321/16792-01/E00-00

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
S170ORRXS	Orange	55.0	36.0	34.0	0.9990	0.0673	5036108511334	15036108996152
S170ORRS	Orange	55.0	36.0	34.0	0.2420	0.0673	5036108283613	15036108773562
S170ORRM	Orange	55.0	36.0	34.0	0.2560	0.0673	5036108283606	15036108773555
S170ORRL	Orange	55.0	36.0	34.0	0.2680	0.0673	5036108283590	15036108773548
S170ORRXL	Orange	55.0	36.0	40.0	0.2350	0.0792	5036108283620	15036108773579
S170ORRXXL	Orange	55.0	36.0	40.0	0.3080	0.0792	5036108283637	15036108773586
S170ORRXXXL	Orange	55.0	36.0	40.0	0.2550	0.0792	5036108283644	15036108773593
S170ORR4XL	Orange	55.0	36.0	40.0	0.2650	0.0792	5036108283576	15036108773524
S170ORR5XL	Orange	55.0	36.0	40.0	0.2750	0.0792	5036108283583	15036108773531