

## Datasheet

Adjustable Elastic Wrist Strap, 4mm Snap, Dark Blue, with Coiled Cord, Black,  
1m long, 4mm and 10mm Socket

RS-798-9297



*Wrist Band*



*Coiled Cord*



### Meets the requirements of EN 61340-5-1 tested per ANSI/ESD S1.1 and IEC 61340-5-1 Clause A.1

#### Wrist Band

- No metal to skin contact
- Choice for those with skin allergies
- Widely adjustable, elasticated fabric band
- Conductive fibres on the inside
- Vermason logo molded into the cap
- Designed to be used with a Coiled Cord with a one megohm current limiting resistor meeting the EN 61340-5-1 Personnel Grounding requirements tested per ANSI/ESD S1.1.
- $R_S$  interior of band:  $< 1 \times 10^5$  ohms Test Method: ANSI/ESD S1.1 (5.2)
- $R_S$  exterior of band:  $> 1 \times 10^7$  ohms Test Method: ANSI/ESD S1.1 (5.2)
- Circumference: Adjustable from 120mm to 200mm
- Colour: Dark Blue
- Termination: 4mm stud
- Weight: 8g

#### Coiled Cord

- 2.5mm polyurethane insulation
- Conductor is high strength 7-end duplex tinsel for strength and flexibility
- Dielectric Strength: Coiled cords withstand 1250 volts DC for at least one minute
- Standard coiled cords are marked and date coded
- Length: 1m
- Colour: black
- Terminations: 10mm and 4mm socket
- 1 megohm  $\pm$  20% current limiting resistor built in each socket

*Unless otherwise noted, tolerance  $\pm$ 10%*

*Specifications and procedures subject to change without notice.*