

A590 - Heat Resistant 250°C Glove

Collection: Heat Gloves

Range: Hand Protection

Materials: Viscose, Cotton, Elastic

Inner Pack: 10

Outer Carton: 120

Product information

The Heat Resistant glove is constructed from viscose, which with a cotton liner, offers a long lasting glove which is heat resistant to contact heat up to 250C. It is seamless, ambidextrous and machine washable.

Heat Gloves

The Heat Protection range provides hand protection against temperatures ranging from 100 degrees to 500 degrees for contact heat, while maintaining exceptional hand dexterity. Trusted to safeguard hands against heat hazards in all work environments.

Hand Protection

A wide and increasing range of hand protection products is available. In order to help cater to every need. Only the best materials and manufacturing methods are used in the production of Portwests' extensive range of Hand Protection products....

Standards

EN ISO 21420: 2020 Dexterity 1
EN 388: 2016 + A1: 2018 (1341X)
EN 407: 2020 (4231XX)



Features

- Provides contact heat protection up to 250°C for 15 seconds
- Robust 7 gauge liner
- Long cuff version
- These gloves are ambidextrous and are suitable for left or right handed users for added functionality
- Glove Length 30cm
- Sold in singles
- Machine washable
- CE certified
- Machine washable to 30°C
- Retail tag which aids presentation for retail sales



PRODUCT SPECIFICATION & TECHNICAL DATASHEET

A590 - Heat Resistant 250°C Glove

Commodity Code: 6116108091

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)

Bracetown Business Park

D15 YN2P, Ireland

Cert No: 2777/21735-02/E00-00

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m³)	EAN13	GTIN/DUN14
A590WHRL	White	56.0	30.0	60.0	0.1080	0.1008	5036108174188	25036108690132
A590WHRXXL	White	56.0	30.0	60.0	0.1100	0.1008	5036108312542	25036108801101