



GE
Lighting



A+

energy class

78

lumens/watt

GE Energy Smart™ - Crown Deco Dimmable

LED6D/P45/827/E14/220-240V/CLS 1/6

93030263

Product information

The LED Crown Deco Dimmable range is the perfect range to replace your Halogen Decorative lamps. It offers superb performances, wide dimming compatibility and very high quality aesthetic with the Silver Paint finishing for Clear bulbs version.

Features and Benefits

- Candle & Spherical
- From 270 to 470 lumens
- Up to 240° beam angle
- Warm White 2700K
- 20000 hours life
- Dimmable
- 25W and 40W Halogen replacement
- 100% retrofit

Application areas



Product data

Product Code	93030263
Bulb Finish	Clear
Bulb Diameter [mm]	45
Nominal Length [mm]	90
Brand	GE BX
Cap/Base	E14

Performance data

Nominal beam angle [°]	160
Energy efficiency class (EEC)	A+
Rated life L70/B50 [h]	20000
Nominal correlated colour temperature (CCT) [K]	2700
Nominal lumens [lm]	470
Colour Rendering Index (CRI) [Ra]	80

Electrical data

Nominal lamp power factor...	0.6
Number of switching cycles	40000
Dimming Capability	Yes
Nominal power [W]	6

Logistic data

DUN Code	10064894533058
EAN Code	0064894533051
Pack Quantity	10
Product status	Available

Downloads & Links

[Go to the catalog site \(HTTP\)](#)

[GE Energy Smart™ - Crown Deco Dimmable Datasheet \(PDF\)](#)

[GE Energy Smart™ - Crown Deco Dimmable Images \(HTTP\)](#)

[Lighting design tools & calculators \(HTTP\)](#)

[Certificate for the Quality Management System of GE Lighting EMEA \(PDF\)](#)

[Certificate for the Environmental Management System of GE Lighting EMEA \(PDF\)](#)