

FEATURES

- Lid equipped with special tab to facilitate single hand opening
- Cable gland design provides external clamping
- IP44 rating
- Screw terminals accept conductors up to 2.5mm² for 16A and 6mm² for 32A types
- Halogen free

RS PRO IP44 Yellow Cable Mount 2P+E Industrial Power Socket, Rated At 32.0A, 110.0V

RS Stock No.: 724-9114



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

These RS Pro Free Sockets are attached to a cable free end, rather than hard mounted, and are for use in industrial applications. The outer casing of these straight sockets is made from engineering plastic and has a cable gland design to provide external clamping. These industrial sockets conform to the latest requirements of British and European standards.

General Specifications

Syntetical Description	Connectors
Pole Format	2P+E
Hour Position	4h
Gender	Female
Body Orientation	Straight
Material	Engineering Plastic
Colour	Yellow
Applications	Providing power for machinery on construction sites, Woodworking machines, Maintenance workshops in the light industry

Electrical Specifications

Type of Current	AC
Current Rating	32A
Voltage Rating	110V
Working Frequency	50Hz; 60Hz
Plug/Socket	Socket
Termination Method	Screw
Cable CSA	6mm ²
Halogen Free	Yes

Mechanical Specifications

Mounting Type	Cable Mount
Cable Inlets	Cable Glands

Protection Category

IP Rating	IP44
------------------	------

Approvals

Compliance/Certifications	EN 60309-1, EN 60309-2
----------------------------------	------------------------



