



KX3 RIPSTOP TROUSERS

DESCRIPTION

Contemporary work trouser made from highly durable ripstop fabric that stretches as you move. Subtle articulation on the knees allow for increased freedom of movement and a high rise back waistband ensures protection in all working positions. Packed with functionality including pre-bent knees, a crotch gusset, two tier knee pad pockets and an adjustable leg length for added convenience. Multi-functional thigh pockets provide secure storage of phones, pens and tools.

COMPOSITION

 **Titanmill Plus Ripstop: 65% Polyester, 35% Cotton Ripstop Weft Stretch, 230g**
 **Black 28-48**

FEATURES

- Stretch ripstop provides superior comfort and increased freedom of movement
- Webbing belt loops for extra durability
- Bottom loading knee pad pockets
- Lower back leg pocket provides quick access whilst kneeling and bending
- Pre-bent knees allow for increased freedom of movement
- 14 pockets for ample storage
- 2 Side pockets
- 2 Back pockets
- 2 side zip pockets for secure storage
- 1 Phone pocket
- 2 Zipped thigh pockets
- 1 Lower leg pocket

STANDARDS

EN 14404: 2004 + A1: 2010 Type 2 Level 0 (When used in combination with S156)

COLOUR / SIZES

SKU	COLOUR	SIZE RANGE
T802BKR	BLACK	28-14

FEATURES



BOTTOM LOADING KNEE PAD POCKETS
Knee pad pockets to facilitate knee pads



UPF 40+
40+ UPF rated fabric to block 98% of UV rays



14 POCKETS
14 pockets for ample storage



ACTIVE STREET WORKWEAR
Active Street Workwear using technical fabrics designed around comfort and performance.

GET THE COLLECTION



TECHINCAL INFORMATION



- Wash dark colours separately
- Wash garment inside out
- Wash garment inside out and fully fastened
- Wash with similar colours

Item	Colour Fit	Len (cm)	Wid (cm)	Hgt (cm)	Weight (Kg)	Cubic (m³)	EAN13	GTIN/DUN14
T802BKR28	Black	43	28	40	.734	2006.666	5036108300389	15036108789907
T802BKR30	Black	43	28	40	.700	2006.666	5036108300396	15036108789914
T802BKR32	Black	43	28	40	.740	2006.666	5036108300402	15036108789921
T802BKR33	Black	43	28	40	.763	2006.666	5036108300419	15036108789938
T802BKR34	Black	43	28	40	.782	2006.666	5036108300426	15036108789945
T802BKR36	Black	43	28	40	.738	2006.666	5036108300433	15036108789952
T802BKR38	Black	43	28	40	.806	2006.666	5036108300440	15036108789969
T802BKR40	Black	43	28	40	.814	2006.666	5036108300457	15036108789976
T802BKR41	Black	43	28	40	.812	2006.666	5036108300464	15036108789983
T802BKR42	Black	43	28	40	.837	2006.666	5036108300471	15036108789990
T802BKR44	Black	43	28	40	.849	2006.666	5036108300488	15036108790002
T802BKR46	Black	43	28	40	.860	2006.666	5036108300495	15036108790019
T802BKR48	Black	43	28	40	.875	2006.666	5036108300501	15036108790026