



CMY Ink Cartridge for BradyJet™ J7300 Colour Label Printer

Order Reference: P-CMY-1

Overview

Get better with BradyJet J7300 inks. Designed specifically for the J7300, BradyJet ink cartridges produce vibrant colours, last long and deliver value in every drop.

- CMY Ink Cartridge delivers vibrant, full-colour labels that demand attention
- Works in tandem with separate K True Black Ink Cartridge to mix more accurate, durable colours
- Ink works with enhanced J7300 label materials topcoat to dry instantly and won't smudge, smear and spot
- Self-contained cartridge drops into printer with a click
- Designed to hold up to 50% more ink for longer use, fewer changeovers and less cartridge waste
- For use with the BradyJet J7300 Colour Label Printer

Specifications

Key Characteristics	Minimum Order Quantity	1
	Article Number	176504
	Order Reference	P-CMY-1
	Total Qty per Pack	1 Cartridge / Box
	Application(s)	Asset tracking, Barcode labelling, Cold temperature labelling, Facility identification, General identification, Hazard communication identification, Inventory and inspection labelling, Laboratory labelling, Lean and 5S labelling, Pipe and valve marking, Temporary labelling, Warehouse marking
	Quantity	1
	Brand	Brady®
	Trade Name	BradyJet™
	Country of Origin	United States of America
	Country of Origin (SAP)	US
Dimensions	Size - Width (mm)	40.64 mm
	Size - Height (mm)	71.12 mm
	Size - Depth (mm)	99.06 mm
	Dimensions	40.64 mm (W) x 71.12 mm (H) x 99.06 mm (D)
	Ink Cartridge Volume	32 ml
Material Characteristics	Colour	Cyan, Magenta, Yellow
Printing Specifications	Print Technology	Inkjet
	Smart Cell	Yes
Compatibility	Printer Compatibility	J7300
Compliance	UNSPSC	45101613
	RoHS Compliance Status	Compliant with Directive 2011/65/EU and 2015/863
	REACH SVHC Status	Part does not contain an SVHC
	REACH Candidate List Date	23 January 2024