

Solenoid coil VACC-S13-18-K4-3U-KS4ME

Part number: 8156761

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Type of actuation	Electric
Mounting position	optional
Switching position indicator	no
Duty cycle	100%
Insulation material class	H
Characteristic coil data	230 V DC: 1.8 W 230 V AC: 40/65 Hz, power 1.8 VA
Permissible voltage fluctuations	-15%/+10%
Explosion protection certification outside the EU	EPL Db (KR) EPL Gb (KR)
Explosion protection	Zone 1 (KR) Zone 21 (KR)
Certificate issuing authority	21-AV4BO-0279X 22-AV4BO-0051X
Explosion ignition protection type for gas	Ex e mb IIC T4, T5, T6
Explosion ignition protection type for dust	Ex tD A21 IP65 T85/T95/T130°C
Explosion ambient temperature	T4, T130 °C: -30 °C ≤ Ta ≤ +60 °C T5, T95 °C: -30 °C ≤ Ta ≤ +60 °C T6, T85 °C: -30 °C ≤ Ta ≤ +50 °C
LABS (PWIS) conformity	VDMA24364 zone III
Degree of protection	IP65
Product weight	330 g
Electrical connection	Terminal box, cable entry thread M20x1.5
Note on materials	RoHS-compliant