

MODULE MOUSSE M4 CLIQUET – DOUILLES 1/4 - 3/8 - 1/2 OGV GRIP®.

MODM.XL1GRPPF



1/4"		<ul style="list-style-type: none"> ⚙️ ED 101T - 102T - 103T ○ EH 103 - 104 - 105 - 106 - 107 ⊕ EP 101T - 102T - 103T ⊖ ES 134.5T - 136.5T - 148T ♻️ EXR 110 - 115 - 120 - 125 - 127 - 130 - 140
		ECR
3/8"		♻️ JX.T T45 - T50 - T55

						
1/4'	R.GRP. 5,5-6-7-8-9-10-11-12-13-14 mm	RL.161 R.180	EF.R180 - 100 mm R.209 - 55 mm R.210 - 100 mm	-	R.235	R.240A
	R.LA 6-7-8-9-10 mm					
1/2'	S.GRP 10 -11-12-13-14-15-16-17-18-19-21-22-24-27-30-32 mm	SXL.161	S.210S - 130 mm S.215S - 250 mm	S.120A	-	S.240A
	S.HLA 16-17-18-19-21 mm					
3/8"	J. 8-9-10-11-12-13-14-15-16-17-18 -19-21-22 mm	JL.161	J.210 - 125 mm J.215 - 250 mm	-	-	J.240A
	J.HLA 11-12- 13-14-15 mm					

1/2'				
	NSI.L 17-19-21 mm	NSTX.L 10-12-14-16-18-20-22-24 mm	NSX.L 30-40-45-50-55-60-70 mm	NSV.L 10-12-14-16-18 mm

SKU	SKU Desc	EAN Code	RRP
MODM.XL1GRPPF	MODULE MOUSSE M4 CLIQUET – DOUILLES 1/4 - 3/8 - 1/2 OGV GRIP®.	3662424116773	€xx.xx