



PRODUCT DATASHEET

Datasheet creation date: 2025/06/02 9:13 (UTC)



6828DDU

Single-Row Deep Groove Ball Bearings

Boundary Dimensions

d	140	mm	Bore diameter
D	175	mm	Outside diameter
B	18	mm	Width
r (min.)	1.1	mm	Chamfer dimension

Basic Load Ratings

Cr	42000	N	Basic dynamic load rating
C0r	48000	N	Basic static load rating

Speeds

Grease	1900	min-1	Grease lubrication
--------	------	-------	--------------------

Abutment and Fillet Dimensions

da (min.)	146.5	mm	Diameter of shaft abutment
da (max.)	148.5	mm	Diameter of shaft abutment
Da (max.)	168.5	mm	Diameter of housing abutment
ra (max.)	1	mm	Radius of shaft or housing fillet

Calculation factors

fo	17.3		Factor
----	------	--	--------

Additional information

z	26		Number of Balls
Dw	10.319	mm	Ball Diameter

Mass

Mass approx.	0.832	kg	Mass approx.
--------------	-------	----	--------------

