

## Features

- Medium Duty
- Industrial castor
- Rotation Swivel
- Fixing Hole
- Rubber
- Corrosion Resistant
- Impact Resistant
- Shock Absorbing

## RS PRO Castor Wheels

RS Stock No.: 0631189



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description







Blue elastic rubber wheel 68 Shore A with black polyamide 6 centre. Hub on shielded ball bearings, roller bearings. In zinc-chromium plated pressed steel, turning on double rim of balls. Assembled with self locking nut. Dust cover ring on the balls.

## General Specifications

<b>Rotation</b>	Swivel
<b>Weight Class</b>	Medium Duty
<b>Load Capacity (Kg)</b>	130
<b>Load Capacity / 4pcs (Kg)</b>	520
<b>Tyre Material</b>	Rubber
<b>Hub Material</b>	Plyamide 6
<b>Bracket Material</b>	Pressed Steel
<b>Includes Brake</b>	No
<b>Features</b>	Corrosion Resistant, Impact Resistant, Shock Absorbing
<b>Applications</b>	Industrial castor

## Operation Environment Specifications

<b>Operating Temperature (Celsius)</b>	-20° to 70°
--	-------------

					
125x36	37	152	12	130	170

## Mechanical Specifications

Mounting Type	Single Bolt
Wheel Diameter (mm)	125
Wheel / Tread Width (mm)	36
Overall Height (mm)	152
Number of Fixing Holes	1
Fixing Hole Size (mm)	12
Hub Bearing Type	Roller bearing
Thread Size (M)	
Stem Height (mm)	
Stem Diameter (mm)	
Hardness of Wheel (Shore A)	68
Levelling Extent (mm)	
Offset (mm)	37
Castor Weight (Kg)	0.868

## Fixing Centres Specifications

Fixing Centres (mm)	
Fixing Centres Length (mm)	
Fixing Centres Width (mm)	

## Fixing Plate Specifications

Fixing Plate Dimensions (mm)	
Fixing Plate Length (mm)	
Fixing Plate Width (mm)	