

PRODUCT-DETAILS

TY125-40-39

TYFAST 3,6X141MM NATUR HEAT STABLIS



General Information

Extended Product Type	TY125-40-39
Product ID	7TCG054360R0130
EAN	5414363060581
Catalog Description	TYFAST 3,6X141MM NATUR HEAT STABLIS
Long Description	Cable Tie, Heat Stabilized Natural Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (221 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 141.48mm (5.57 Inches), Width of 3.556mm (0.140 Inches), Thickness of 1.17mm (0.046 Inches), Tensile Strength Rating of 180 Newtons (40 Pounds), UL Tensile Strength Rating of 133 Newtons (30 Pounds), Bulk Pack

Ordering

EAN	5414363060581
UPC	786210788616

Container Information

Package Level 1 Units	1000 piece
Package Level 1 Width	12 in 305 mm
Package Level 1 Height	3 in 76 mm
Package Level 1 Depth / Length	12 in 305 mm
Package Level 2 Units	10000 piece

Package Level 2 Width	11.4 in 290 mm
Package Level 2 Height	9.1 in 231 mm
Package Level 2 Depth / Length	15 in 381 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Catamount
Bundle Diameter	1.25 in 31.75 mm
Color	Natural
Effective Date	20011127
Lock Type	Plastic Pawl
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	OTHER PLASTICS ITEMS
Product Type	Heat Stabilized
Tensile Strength	40 lb 180 N
Thickness	0.046 in 1.17 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY125-40-39
Declaration of Conformity - CE	9AKK107492A9843
Instructions and Manuals	TY125-40-39

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

