MINIATURE MICRO SWITCHES MV25 - SERIES

ELECTRICAL RATING

LOAD RATINGS (for micro switch with 400/200 gms. actuating force)

AC 16 Amp at 250V 5 Amp at 440V 0.6 Amp at 110V 0.3 Amp at 220V DC (Inductive) 0.1 Amp at 110V 0.05 Amp at 220V

Voltage proof 1500 VAC between each terminal and

1000VAC between open contacts

Contact resistance 15 milliohms max. (initial)
Insulation resistance 100Mohms min. at 500VDC
Electrical life 100,000 operations at rated load

Mechanical life 10,000,000 operations

ENVIRONMENTAL

Temperature -55°C to +85°C

APPLICATIONS:

Automotive, Machine control, Telecommunication equipments, Vending equipments, Security Products, Defence, Business automation machines, Instruments

Note: (i) For 100 gms. actuating force rated current is 10 A at 250V AC

For 50 gms. actuating force rated current is 6 A at 250V AC

(ii) Knob Colour : Black - 400 gms., Red - 200 gms., Green - 100 gms., Yellow - 50 gms. (iii) OF : Operating force FP : Free position OP : Operating position


RF: Release force MD: Movement differential

OT :Over travel PT :Pre travel

Basic switch (quick connect [4.75 x 0.5mm.] terminals)


Ordering code	Actuating force	Release force
MV25 34	400 gms. (max.)	80 gms. (min.)


Pretravel (PT) 1.2 mm. (max.)
Overtravel 1.0 mm.
Movement differential 0.4 mm. (max.)
Operating position (OP) 14.7±0.4 mm.






CIRCUIT FORM







All dimensions are in mm.

Due to continuous improvement in products, we reserve the right to alter specifications without prior notice