

Verstellbares Windeisen

Adjustable tap wrenches








Art. 601 GD

DIN 1814
aus Zinkdruckguss (GD).

DIN 1814
made of zinc pressure casting (GD).



 CODE	No.	 mm	M Mf	Ww	G	 mm	 g	 EAN-CODE 4026558.....
04971	0	2 - 5	M 1 - M 8	1/16 - 5/16		125	50	049717
04972	1	2 - 6	M 3 - M 10	1/8 - 3/8		180	90	049724
04973	1 1/2	2,5 - 8	M 3 - M 12	1/8 - 1/2	G 1/8	200	100	049731
04974	2	4 - 9	M 4 - M 12	3/16 - 5/8	G 1/8 - G 3/8	280	280	049748
04975	3	4,9 - 12	M 5 - M 20	1/4 - 3/4	G 1/8 - G 1/2	375	670	049755
04976	4	5,5 - 16	M 10 - M 27	3/8 - 1	G 1/8 - G 3/4	500	1450	049762
04977	5	7 - 20	M 14 - M 33	5/8 - 1 1/4	G 1/4 - G 1	750	1550	049779