

Datasheet

RS Pro #3320BC Digital Thermometer, 1 Input Desk, Wall

RS Stock No: 427-433



Product Details

RS Pro digital thermometer comes with 1 input desk, 17 mm high digital display and self adhesive hook and loop strips for surface mounting. It has an operating temperature of 0 to +50°C.

Features and Benefits

- Temperature range from 0 to +50°C
- 1 x AAA battery type
- Wall mountable type

**Specifications:**

Absolute Maximum Temperature Measurement	+50°C
Application	Wall/Desk
Battery Type	AAA
Best Accuracy	±2%
Dimensions	63 x 45 x 15 mm
Height	15 mm
Length	63 mm
Number of Temperature Inputs	1
Resolution	0.1°C
Temperature Scale	Centigrade
Thermometer Type	Desk, Wall
Width	45 mm
Instrument Measurement Range	0 to +50°C