


MARQUARDT

SERIES 1800 - SINGLE AND DOUBLE-POLE ROCKER SWITCHES

TO 12 (4) A 250 V AC

single-pole 	ON/OFF switch (SPST)	1801.1102	1801.1119	1801.1146	1801.1403	1801.1601	1801.1912	1801.2106	1801.2402	1801.2702	1801.5429	1801.6101	1801.6102	1801.6109	1801.6115	1801.6158
Voltage lamp in V																
Actuator color / printing																
Housing color																
12 (4) A 250 V AC 1E4																
10 (4) A 250 V AC 1E4		●	●	●	●	●	●	●	●	●	●	●	●	●	●	
8 (8) A 250 V AC 5E4																
6 (4) A 250 V AC 5E4		●	●	●	●	●	●	●	●	●	●	●	●	●	●	
6 (2) A 250 V AC 1E4																
4 (3) A 250 V AC 6E3																
4 (2) A 250 V AC 1E4																
30 mA 12 V 5E4																
30 mA 12 V DC 5E4																●
15 A 250 V AC 1 1/2 HP																
15 A 125 V AC 3/4 HP																
10 A 250 V AC 1/2 HP																
10 A 125 V AC 1/3 HP																
6 A 250 V AC 1/2 HP		●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
6 A 125 V AC 1/4 HP		●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
6 A 125 - 250 V AC 1/8 HP																
6 A 125 V AC 1/10 HP																
4 A 250 V AC 1/10 HP																
Connection type																
Connection description		4.8	4.8	4.8	4.8	4.8	4.8									
Inrush current in A (capacitive)		50	50	50	50	50	50	50	50	50	50	50	50	50	50	
Contact distance in mm		≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3
Contact material		Ag	Ag	Ag	Ag	Ag	Ag	Ag								
EN 60335 cap. 30 conform *G*							●									●
Miscellaneous					with dust cap/black connections 30° angled				installation depth 13.2	installation depth 28.1						
Stock version		●	●	●	●			●				●	●	●	●	