

**MNX ABS 175/75 HT**



Sample photo

**Order symbol:** ABS 175/75 HT  
**Product nbr:** 6081920  
**Description:** Enclosure, ABS  
**Remarks:** Smoked transparent cover

**EAN:** 6418074024473  
**El. number:**  
 Finland 3422258  
 Denmark 8212023903  
 Italy 7362113  
 Sweden 2535864

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:	L	W	H	Rating:
mm:	180	180	75	<b>Electrical insulation:</b> Totally insulated <b>Halogen free (DIN/VDE 0472, Part 815):</b> Yes <b>Flammability Rating (UL 746 C 5):</b> UL 94 HB <b>Glow Wire Test (IEC 695-2-1) °C:</b> 650 <b>NEMA Class:</b> NEMA 1, 4, 4X, 6, 12, 13 <b>Ingress Protection (EN 60529):</b> IP 66/67 <b>Impact Resistance (EN 50102):</b> IK 07
inch:	7.1	7.1	3	

Materials:	
<b>Material:</b>	ABS
<b>Gasket material:</b>	TPE
<b>Base colour:</b>	RAL 7035
<b>Cover colour:</b>	Smoked grey
<b>Cover screws material:</b>	Polyamide
<b>Cover screws colour:</b>	Black

Temperatures:	
<b>Short term:</b>	-40 ... 80 °C
<b>Continuous:</b>	-40 ... 60 °C
<b>Short term:</b>	-40 ... 175 °F
<b>Continuous:</b>	-40 ... 140 °F

Accessories:	
MIV 175	Mounting plate (Galvanized steel)
MIN 15	DIN-15 Mounting rail
MIV 15	DIN-35 Mounting rail
FP A 175/180	Front plate (Aluminium)
HFP 180	Front plate hinge series (2 pcs)
FP 22046	Wall fastening lug (4 pcs)

Certificates:
Fimko
Europe EN 50298: 1998
Gost R

