

THERMOMARK-RIBBON 25-WMSU - Ink ribbon



0803390

<https://www.phoenixcontact.com/gb/products/0803390>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF..., length: 300 m, roll length: 300 m, width: 25 mm, color: black

Commercial data

Item number	0803390
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG1223
Product key	BG1223
Catalog page	Page 42 (C-3-2019)
GTIN	4055626052038
Weight per piece (including packing)	72.2 g
Weight per piece (excluding packing)	74.5 g
Customs tariff number	96121010
Country of origin	US

THERMOMARK-RIBBON 25-WMSU - Ink ribbon



0803390

<https://www.phoenixcontact.com/gb/products/0803390>

Technical data

Product properties

Product type	Ink ribbon
Scope of delivery	Ink ribbon

Marking

Identification technology	Thermal transfer
---------------------------	------------------

Dimensions

Width	25 mm
Length	300 m
Length of roll	300 m

Material specifications

Color	black (RAL 9005)
Material	Polyolefin-compatible ink coating

Environmental and real-life conditions

Ambient conditions

Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	24 months after production date.

THERMOMARK-RIBBON 25-WMSU - Ink ribbon



0803390

<https://www.phoenixcontact.com/gb/products/0803390>

Classifications

ECLASS

ECLASS-13.0	19140614
-------------	----------

ETIM

ETIM 9.0	EC001694
----------	----------

UNSPSC

UNSPSC 21.0	44103100
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------