

18345-231 Winter Jacket

CLIMASCOT® lining - Ladies fit - breathable - wind- and waterproof

MASCOT® ACCELERATE



XS	S	M	L	XL	2XL	3XL	4XL	5XL
----	---	---	---	----	-----	-----	-----	-----

100% polyester
210 g/m²



Ripstop. Hydrostatic pressure test > 10,000 mmH₂O according to EN ISO 811.

Industrial care category C2

CLIMASCOT® LIGHTWEIGHT INSULATION
CORDURA® FABRIC

Certifications



Logo

You should choose a transfer that can be heated at a maximum of 145 degrees with consideration to print on the product. Remember to check the washing instructions for the chosen transfer before washing the product.

Logo placement:

- Workwear logo stretch. Left breast pocket. Max 9x5 cm/3.5x1.9 inches
- Workwear logo stretch. Over left breast pocket. Max 9x3 cm/3.5x1.1 inches
- Workwear logo stretch. Right breast. Max 8x6 cm/3.1x2.3 inches
- Workwear logo stretch. Mid-back. Max 28x20 cm/11x 7.8 inches
- Workwear logo. Special placement. Contact to discuss further



- Specially designed and fitted for women.
- Breathable, wind and waterproof with taped seams.
- Unique CLIMASCOT® insulation provides warmth without bulk. Lightweight, soft CLIMASCOT® insulation takes up almost no space when compressed.
- Detachable lined hood with adjustable elastic drawstring.
- Fastening with zip and internal storm flap, so the wind is kept out.
- Sleeves with reinforcement of CORDURA®.
- Interior zipper at lower back for logo printing / embroidery.
- Extra visibility with the help of reflectors.

Technical info

Ladies fit. Breathable, wind and waterproof. Taped seams. CLIMASCOT® Lightweight Insulation. Detachable lined hood with adjustable drawstring. Fastening with zip and internal storm flap. Inner pocket with zip. Detachable ID card holder. Front pockets with zip. Adjustable elastic drawstring at waist. Zip at lower back for logo printing/ embroidery. Sleeves with reinforcement of CORDURA®. Rib (hidden in storm flap) at cuffs. With print and reflectors.

User

