



Part Number : 1301040021
Product Description : Haztex Hazardous
Location 26W Fluorescent Hand Lamp Only
Series Number : 130104
Status : Active
Product Category : Lamps and Lights
Engineering Number : 1090-HZ



Product Environment Compliance

Compliance

GADSL/IMDS	Not Reviewed
China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
--------	--------

Category	Lamps and Lights
Series	130104
Description	Haztex Hazardous Location 26W Fluorescent Hand Lamp Only
Comments	Class I, Division 1, Groups C and D (flammable gases and vapors); Class II, Division I, Groups F and G (ignitable dust); Class I, Zone 1, Group IIB (UL)
NEMA Configuration	N/A
Product Name	Haztex
Type	Hand Lamps, Specialty Light
UPC	78678861277

Agency

UL	E30252
----	--------

Electrical

Lamp Wattage - Maximum	26W
Lumens	1800
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Physical

Bulb Type	Fluorescent
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	100.08mm (3.940")
Duty	Hazardous
Guard Included	Yes
Guard Type	Cast Aluminum
Height	482.60mm (19.000")
Lamp Type	PL-C 26/41/4P
Length	N/A
Material - Globe	Tempered Soda-Lime Glass
Material - Guard	Cast Aluminum
Mounting Style	Hand Held

Net Weight	2322.392/g
Outlet	None
Packaging Type	Carton

This document was generated on Mar 27, 2025