

# TM-RIBBON 110 WH 101 - Ink ribbon



1099966

<https://www.phoenixcontact.com/in/products/1099966>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ink ribbon, For THERMOMARK roll printers for printing the product group material off the roll:  
PML-T..., length: 60 m, roll length: 60 m, width: 110 mm, color: white

## Commercial data

Item number	1099966
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG1
Product key	BG1223
GTIN	4055626951317
Weight per piece (including packing)	149.5 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	96121010
Country of origin	JP

# TM-RIBBON 110 WH 101 - Ink ribbon

1099966

<https://www.phoenixcontact.com/in/products/1099966>



## Technical data

### Product properties

Product type	Ink ribbon
--------------	------------

### Marking

Identification technology	Thermal transfer
---------------------------	------------------

### Dimensions

Width	110 mm
Length	60 m
Length of roll	60 m

### Material specifications

Color	white (RAL 9010)
-------	------------------

### Environmental and real-life conditions

#### Ambient conditions

Recommended ambient temperature (storage/transport)	30 °C ... 80 °C
Recommended humidity (storage/transport)	5 % ... 35 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	1 Year

# TM-RIBBON 110 WH 101 - Ink ribbon



1099966

<https://www.phoenixcontact.com/in/products/1099966>

## Classifications

### ECLASS

ECLASS-11.0	19140614
ECLASS-12.0	19140614
ECLASS-13.0	19140614

### ETIM

ETIM 9.0	EC001694
----------	----------

### UNSPSC

UNSPSC 21.0	44103100
-------------	----------

# TM-RIBBON 110 WH 101 - Ink ribbon



1099966

<https://www.phoenixcontact.com/in/products/1099966>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

# TM-RIBBON 110 WH 101 - Ink ribbon

1099966

<https://www.phoenixcontact.com/in/products/1099966>



## Accessories

### THERMOMARK ROLL 2.0 - Thermal transfer printer

1085260

<https://www.phoenixcontact.com/in/products/1085260>



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

---

### THERMOMARK ROLLMASTER 300 - Thermal transfer printer

0804501

<https://www.phoenixcontact.com/in/products/0804501>



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Support CD includes user manuals in several languages, links to firmware, drivers, and planning and marking software. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

## TM-RIBBON 110 WH 101 - Ink ribbon

1099966

<https://www.phoenixcontact.com/in/products/1099966>



## THERMOMARK ROLLMASTER 600 - Thermal transfer printer

0804663

<https://www.phoenixcontact.com/in/products/0804663>



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Support CD includes user manuals in several languages, links to firmware, drivers, and planning and marking software. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

---

## THERMOMARK ROLL - Thermal transfer printer

5146477

<https://www.phoenixcontact.com/in/products/5146477>



Thermal transfer printer, 300 dpi, incl. European power cable, US power cable, and USB cable. DVD with CLIP PROJECT advanced planning and marking software, user manuals in various languages, Windows® printer driver, and firmware. German/English user manual in DIN A5 format, EML (20x8)R roll of labels, white, with 1000 labels, and ink ribbon: 50 m

# TM-RIBBON 110 WH 101 - Ink ribbon

1099966

<https://www.phoenixcontact.com/in/products/1099966>



## THERMOMARK X1.2 - Thermal transfer printer

5146231

<https://www.phoenixcontact.com/in/products/5146231>



Thermal transfer printer, weight: 10 kg, length: 0.446 m, width: 242 mm, height: 274 mm, color: gray

---

## THERMOMARK W2 - Thermal transfer printer

5146147

<https://www.phoenixcontact.com/in/products/5146147>



Thermal transfer printer for material off the roll, incl. Euro/US power cable, USB cable, and perforation knife. Support CD includes user manuals in several languages, links to firmware, drivers, and planning and marking software. Operating instructions printed in German and English.

# TM-RIBBON 110 WH 101 - Ink ribbon

1099966

<https://www.phoenixcontact.com/in/products/1099966>



## THERMOMARK S1.1 - Thermal transfer printer

5146257

<https://www.phoenixcontact.com/in/products/5146257>



Thermal transfer printer, weight: 2 kg, length: 0.25 m, width: 230 mm, height: 170 mm, color: gray

---

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

[info@phoenixcontact.co.in](mailto:info@phoenixcontact.co.in)