

Datasheet

RS Pro 30 kW 3P Star Delta Starter, 400 V ac, 3 Phase, IP65

RS Stock No: **725-5563**



Product Details

RS Pro 30 kW 3-phase star delta starter, measures 220 x 280 x 170 mm. It has a range of enclosed star delta motor starter which combine high performance and low cost. The range includes options with and without isolator and support for motors from 11 kW to 30 kW. It has moulded plastic case to provide IP65 ingress protection.

Features and Benefits

- Operating temperature range: -25 to +60°C
- Starting time up to 12s and a maximum of 30 operations per hour
- Voltage rating of 400 V ac
- 3 poles
- Star delta starter
- Compliant with standards IEC/EN 60947-1 and IEC/EN 60947-4-1

**Specifications:**

Additional Features	Disconnect Switch Not Included
Enclosure	Yes
Motor Starter Type	Star Delta
Phase	3
Standards Met	RoHS Compliant; IEC/EN 60947-1; IEC/EN 60947-4-1
Overall Depth	170 mm
Overall Length	220 mm
Overall Width	280 mm
Current Rating	32 to 38 A
IP Rating	IP65
Number of Poles	3
Power Rating	30 kW
Voltage Rating	400 V ac
Maximum Motor Current	60 A
Motor Supporting Range	11 to 30 kW
Operating Temperature	-25 to +60°C