

## Features

- "K" NiCr-Ni Type Thermocouples
- Max. operating temperature 400°C
- SKP5 Copper
- Sensor type DIN/IEC-584 "K" NiCr-Ni
- Cable type Fiber glass+Fiber glass+Braided
- Immersion Length 26mm
- Cable Length 2meter

## RS PRO Bayonet Type Cable Lug "K" Type Thermocouples

RS Stock No: 0350394



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

Standard Bayonet "K" Type Thermocouples Temperature Sensor

Diameter(M): 9,4mm

Immersion Length(L): 26mm

Cable Length(K): 2m

Applications Fields

- Machinery Manufacturing
- Panel Manufacturing
- Production and Test Equipment
- Food, Chemical, Textile Sectors
- Industrial Control Applications


## General Specifications

Max. Operating Temperature	-50 °C / +400 °C
Standard cable types	Fiber glass + fiber glass + braided wire
Sensor type	"K" Type Thermocouples (DIN/IEC-584)
Protection tube material	Nickel coated brass
Connector	SKP5 Copper

## Mechanical Specifications

Diameter (M)	9,4mm
Immersion Length (L)	26mm
Cable Length (K)	2m

## Electrical Connection



### Thermoelement Connections

