



COMMUTATING CHOKE FOR CONVERTER;  
 PHASES:3; UN1(V):400; ITHMAX 1(A) / F1(HZ):140  
 /50; I LN (A):126; UK(%):4; LN(MH):0,149; TA/ISOKL:40  
 /H; IP00; TYPE OF TERMINALS:FLAT-TYPE  
 TERMINAL; EN 61558-2-20 >CHOKE<

Figure similar

General technical data		
Product designation		Kommut.-Drossel f. Stromrichter
Phase number		3
Type of voltage		AC
Operating voltage rated value	V	400
Operating frequency rated value	Hz	50
Current		
• at AC		
— rated value	A	126
— maximum	A	140
• at DC rated value	A	171.5
Inductivity rated value	H	0.00015
Relative inductive drop in voltage on the measurement level current, voltage and frequency	%	4
Power loss [W] of the coil	W	135
Power loss [W] of the iron core	W	55

Mechanical data

Type of electrical connection for main current circuit		flat connector
Width	m	0.225
Height	m	0.21
Depth	m	0.16

#### Ambient conditions

Thermal class acc. to IEC 60085		H
Ambient temperature rated value	°C	40
Protection class IP		IP00

#### Certificates/ approvals

General Product Approval	other
--------------------------	-------

[Confirmation](#)



#### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<https://www.siemens.com/ic10>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=4EU2522-2BA00-0AA0>

**Cax online generator**

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4EU2522-2BA00-0AA0>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/4EU2522-2BA00-0AA0>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=4EU2522-2BA00-0AA0&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4EU2522-2BA00-0AA0&lang=en)

last modified:

07/28/2020